

Garant GRIDLINE

**Vario workbench with drawer casing 24G, cupboard, height 950 mm, Bamboo worktop, 20×20G, Worktop length: 2000/T3mm****Order data**

Order number	922791 2000/T3
GTIN	4062406085469
Item class	9GG

**Description****Version:**

Workbench in sturdy steel construction. Support legs 50 mm wide with cross bracing. Feet with plastic pads, do not damage the floor. With 1 pair of stabilising plates for stiffening. Casing 24G can be locked centrally with a cylinder lock. **100% full extension drawers** with differential runners and 75 kg load capacity.

**Fitted with:**

Drawer front height, mm: 75, 75, 100

Door height, mm: 525

Number of height-adjustable storage shelves: 1

**Supplied with:**

1 pc. support leg, 1 pc. pair of stabilising plates, casing with drawers and door, worktop.

**Colour:**

Casing body, support legs and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

**Note:**

Supplied for self-assembly, saving freight costs. Delivered unassembled.

**Technical description**

Drawer usable area in G	20×20
Worktop depth	750 mm
Worktop thickness	50 mm

Drawer usable depth	500 mm
Series	vario
Workbench/desk load capacity - maximum distributed load (on wood)	800 kg
Drawer body usable height	800 mm
Drawer usable depth in G	20
Drawer body height	900 mm
Weight	143 kg
Drawer body width	600 mm
Drawer usable width in G	20
Drawer usable width	500 mm
Drawer body depth	650 mm
Worktop length	2000 mm
Height	950 mm
Number of drawers	3
Design version	Steel hollow section construction
Material thickness	1 mm
Workbench height	950 mm
Drawer/pull-out shelf load capacity	75 kg
Insert thickness	50 mm
Drawer runner extension (partial/full extension)	100 %
Door opening angle	180 degrees
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20×20G
Type of product	Workbench

## Accessories

Cleaner and care oil set Type 1	926403 1
Drawer Drawer front height 100 mm	927800 100
easyPick small parts storage bins set Drawer front height / type 75/2	950300 75/2
Slide handle for GridLine Type KO12	914226 KO12
Lock plate for GridLine Type KO21	914227 KO21
Workshop set Number of tools 22	955071 22
Screwdriver set Number of tools 10	953521 10
Overlay of plasticised PVC transparent Width 2000 mm	951951 2000
Drawer Drawer front height 75 mm	927800 75
Slotted dividers / plain dividers set Drawer front height / type 75/3	950320 75/3
easyPick small parts storage bins set Drawer front height / type 75/3	950300 75/3
Slotted dividers / plain dividers set Drawer front height / type 100/2	950320 100/2
Ribbed rubber mat for drawers Dimension in G 20X20	951910 20X20
Slotted dividers / plain dividers set Drawer front height / type 75/2	950320 75/2
Comfort Close drawer closure damping system Load capacity of the drawer 75 kg	950180 75
Mat for drawers Dimension in G 20X20	951830 20X20
Slotted dividers / plain dividers set Drawer front height / type 75/1	950320 75/1
easyPick small parts storage bins set Drawer front height / type 75/1	950300 75/1
Non-slip mats set for drawers,5 pieces Dimension in G 20X20	951885 20X20
Pliers set Number of tools 5	954305 5
Slotted dividers / plain dividers set Drawer front height / type 100/1	950320 100/1
	950320 100/3

Slotted dividers / plain dividers set Drawer front height /  
type 100/3

Casing 24G with door hinged on the right / drawers  
Height / number of drawers 900/3

927610 900/3

Support leg Height 900 mm

927000 900

Stabilising plate Type 1

927122 1

Worktop thickness 50 mm of bamboo strips glued cross-  
wise Worktop length 2000 mm

926001 2000