

Garant GRIDLINE

Vario workbench with drawer casing 24G, cupboard, height 850 mm, Eluplan worktop, dark, 20×20G, Worktop length: 1500/T2mm**Order data**

Order number	922787 1500/T2
GTIN	4062406085438
Item class	9GG

Description**Version:**

Workbench in sturdy steel construction. Support legs 50 mm wide with cross bracing. Feet with plastic pads, do not damage the floor. With 1 pair of stabilising plates for stiffening. Casing 24G can be locked centrally with a cylinder lock. **100% full extension drawers** with differential runners and 75 kg load capacity.

Fitted with:

Drawer front height, mm: 75#75

Door height, mm: 525

Number of height-adjustable storage shelves: 1

Supplied with:

1 pc. support leg, 1 pc. pair of stabilising plates, casing with drawers and door, worktop.

Colour:

Casing body, support legs and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Note:

Supplied for self-assembly, saving freight costs. Delivered unassembled.

Technical description

Drawer body usable height	700 mm
Drawer usable depth	500 mm

Workbench/desk load capacity - maximum distributed load (on wood)	800 kg
Drawer usable width	500 mm
Drawer body height	800 mm
Drawer body width	600 mm
Series	vario
Weight	119 kg
Drawer usable area in G	20×20
Height	850 mm
Drawer usable width in G	20
Drawer usable depth in G	20
Drawer body depth	650 mm
Worktop length	1500 mm
Number of drawers	2
Worktop thickness	50 mm
Worktop depth	750 mm
Design version	Steel hollow section construction
Material thickness	1 mm
Workbench height	850 mm
Drawer/pull-out shelf load capacity	75 kg
Insert thickness	50 mm
Drawer runner extension (partial/full extension)	100 %
Door opening angle	180 degrees
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20×20G
Type of product	Workbench

Accessories

Lock plate for GridLine Type KO21	914227 KO21
Slide handle for GridLine Type KO12	914226 KO12
Drawer Drawer front height 75 mm	927800 75
Casing 24G with door hinged on the right / drawers Height / number of drawers 800/2	927610 800/2
Worktop with dark grey plastic coating (Eluplan) Worktop length 1500 mm	926241 1500
Support leg Height 800 mm	927000 800
Stabilising plate Type 1	927122 1