

Garant GRIDLINE

## Vario workbench with 2 drawer casings 24G, height 850 mm, Bamboo worktop, 20×20G, Worktop length: 2000/6+7mm



### Order data

Order number	922801 2000/6+7
GTIN	4062406085513
Item class	9GG

### Description

#### Version:

Workbench in sturdy steel construction. Drawer casing 24G can be locked centrally with cylinder lock. **100% full extension drawers** with differential runners and 75 kg load capacity.

#### Fitted with:

Drawer front height (left) mm: 50, 75, 100, 125, 150, 200

Drawer front height (right) mm: 75; 75; 75; 75; 100; 100; 200

#### Supplied with:

2 × drawer casings, worktop.

#### Colour:

Casing body, support legs and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

#### Note:

Supplied for self-assembly, saving freight costs. Delivered unassembled.

### Technical description

Drawer body width	600 mm
Drawer body depth	650 mm
Drawer usable depth	500 mm
Height	850 mm
Drawer usable area in G	20×20

Drawer usable width	500 mm
Worktop thickness	50 mm
Drawer usable depth in G	20
Workbench/desk load capacity - maximum distributed load (on wood)	1000 kg
Drawer usable width in G	20
Worktop length	2000 mm
Worktop depth	750 mm
Number of drawers	13
Weight	219 kg
Drawer body usable height	700 mm
Series	vario
Material thickness	1 mm
Workbench height	850 mm
Drawer/pull-out shelf load capacity	75 kg
Insert thickness	50 mm
Drawer runner extension (partial/full extension)	100 %
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20x20G
Type of product	Workbench

## Accessories

Drawer Drawer front height 75 mm	927800 75
Drawer Drawer front height 200 mm	927800 200
Drawer Drawer front height 100 mm	927800 100
Drawer Drawer front height 125 mm	927800 125

Drawer Drawer front height 150 mm	927800 150
Lock plate for GridLine Type KO21	914227 KO21
Drawer Drawer front height 50 mm	927800 50
Drawer casing 24G with drawers Height / number of drawers 800/7	927600 800/7
Drawer casing 24G with drawers Height / number of drawers 800/6	927600 800/6
Worktop thickness 50 mm of bamboo strips glued cross-wise Worktop length 2000 mm	926001 2000