

Garant GRIDLINE

Vario workbench with drawer casing 24G, cupboard, height 950 mm, Beech marine ply worktop, 20×20G, Worktop length: 1500/T3mm**Order data**

Order number	922794 1500/T3
GTIN	4062406085476
Item class	9GG

Description**Version:**

Workbench in sturdy steel construction. Support legs 50 mm wide with cross bracing. Feet with plastic pads, do not damage the floor. With 1 pair of stabilising plates for stiffening. Casing 24G can be locked centrally with a cylinder lock. **100% full extension drawers** with differential runners and 75 kg load capacity.

Fitted with:

Drawer front height, mm: 75, 75, 100

Door height, mm: 525

Number of height-adjustable storage shelves: 1

Supplied with:

1 pc. support leg, 1 pc. pair of stabilising plates, casing with drawers and door, worktop.

Colour:

Casing body, support legs and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Note:

Supplied for self-assembly, saving freight costs. Delivered unassembled.

Technical description

Drawer usable depth	500 mm
Drawer body depth	650 mm

Number of drawers	3
Drawer usable depth in G	20
Drawer body height	900 mm
Drawer body usable height	800 mm
Height	950 mm
Drawer body width	600 mm
Drawer usable width	500 mm
Series	vario
Drawer usable area in G	20×20
Drawer usable width in G	20
Workbench/desk load capacity - maximum distributed load (on wood)	800 kg
Worktop thickness	50 mm
Worktop length	1500 mm
Worktop depth	750 mm
Weight	129 kg
Design version	Steel hollow section construction
Material thickness	1 mm
Workbench height	950 mm
Drawer/pull-out shelf load capacity	75 kg
Insert thickness	50 mm
Drawer runner extension (partial/full extension)	100 %
Door opening angle	180 degrees
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20×20G
Type of product	Workbench

Accessories

Drawer Drawer front height 75 mm	927800 75
Lock plate for GridLine Type KO21	914227 KO21
Slide handle for GridLine Type KO12	914226 KO12
Drawer Drawer front height 100 mm	927800 100
Casing 24G with door hinged on the right / drawers Height / number of drawers 900/3	927610 900/3
Support leg Height 900 mm	927000 900
Stabilising plate Type 1	927122 1
Worktop thickness 50 mm of beech marine ply Worktop length 1500 mm	926081 1500