

Garant GRIDLINE

**Vario workbench with drawer casing 24G, cupboard, height 950 mm, Eluplan worktop, dark, 20×20G, Worktop length: 1500/T3mm****Order data**

|              |                |
|--------------|----------------|
| Order number | 922797 1500/T3 |
| GTIN         | 4062406085490  |
| Item class   | 9GG            |

**Description****Version:**

Workbench in sturdy steel construction. Support legs 50 mm wide with cross bracing. Feet with plastic pads, do not damage the floor. With 1 pair of stabilising plates for stiffening. Casing 24G can be locked centrally with a cylinder lock. **100% full extension drawers** with differential runners and 75 kg load capacity.

**Fitted with:**

Drawer front height, mm: 75, 75, 100

Door height, mm: 525

Number of height-adjustable storage shelves: 1

**Supplied with:**

1 pc. support leg, 1 pc. pair of stabilising plates, casing with drawers and door, worktop.

**Colour:**

Casing body, support legs and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

**Note:**

Supplied for self-assembly, saving freight costs. Delivered unassembled.

**Technical description**

|                     |         |
|---------------------|---------|
| Worktop length      | 1500 mm |
| Drawer usable depth | 500 mm  |

|   |  |
|---|--|
| Drawer usable area in G   | 20×20  |
| Drawer usable width in G  | 20   |
| Workbench/desk load capacity - maximum distributed load (on wood) | 800 kg   |
| Drawer body depth   | 650 mm   |
| Drawer usable depth in G  | 20   |
| Worktop thickness   | 50 mm  |
| Drawer body width   | 600 mm   |
| Drawer usable width   | 500 mm   |
| Height  | 950 mm   |
| Weight  | 129 kg   |
| Drawer body usable height   | 800 mm   |
| Worktop depth   | 750 mm   |
| Series  | vario  |
| Drawer body height  | 900 mm   |
| Number of drawers   | 3  |
| Design version  | Steel hollow section construction                              |
| Material thickness  | 1 mm   |
| Workbench height  | 950 mm   |
| Drawer/pull-out shelf load capacity                               | 75 kg  |
| Insert thickness  | 50 mm  |
| Drawer runner extension (partial/full extension)                  | 100 %  |
| Door opening angle  | 180 degrees  |
| Cylinder lock   | modular lock barrel  |
| Colour selection  | RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003 |
| Product name attribute  | 20×20G   |
| Type of product   | Workbench  |

## Accessories

|   |              |
|---|--------------|
| Drawer Drawer front height 75 mm  | 927800 75    |
| Slide handle for GridLine Type KO12   | 914226 KO12  |
| Drawer Drawer front height 100 mm   | 927800 100   |
| Lock plate for GridLine Type KO21   | 914227 KO21  |
| Worktop with dark grey plastic coating (Eluplan) Worktop length 1500 mm             | 926241 1500  |
| Stabilising plate Type 1  | 927122 1     |
| Support leg Height 900 mm   | 927000 900   |
| Casing 24G with door hinged on the right / drawers Height / number of drawers 900/3 | 927610 900/3 |