

Garant GRIDLINE

## Vario workbench with 2 drawer casings 24G, height 850 mm, Beech marine ply worktop, 20×20G, Worktop length: 2000/7+2Tmm



### Order data

Order number	922804 2000/7+2T
GTIN	4062406085582
Item class	9GG

### Description

#### Version:

Workbench in sturdy steel construction. Drawer casing 24G can be locked centrally with cylinder lock. **100% full extension drawers** with differential runners and 75 kg load capacity.

#### Fitted with:

Drawer front height (left) mm: 75; 75; 75; 75; 100; 100; 200

Drawer front height (right) mm: 75#75

Door height (right) mm: 525

Number of height-adjustable storage shelves (right): 1

#### Supplied with:

2 × drawer casings, worktop.

#### Colour:

Casing body, support legs and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

#### Note:

Supplied for self-assembly, saving freight costs. Delivered unassembled.

### Technical description

Worktop depth	750 mm
Number of drawers	9
Drawer body usable height	700 mm
Drawer usable width in G	20

Weight	185 kg
Worktop thickness	50 mm
Worktop length	2000 mm
Workbench/desk load capacity - maximum distributed load (on wood)	1000 kg
Height	850 mm
Drawer body depth	650 mm
Drawer usable depth	500 mm
Drawer body width	600 mm
Drawer usable depth in G	20
Drawer usable area in G	20×20
Series	vario
Drawer usable width	500 mm
Door opening angle	180 degrees
Material thickness	1 mm
Workbench height	850 mm
Drawer/pull-out shelf load capacity	75 kg
Insert thickness	50 mm
Drawer runner extension (partial/full extension)	100 %
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20×20G
Type of product	Workbench

## Accessories

Drawer Drawer front height 200 mm	927800 200
Lock plate for GridLine Type KO21	914227 KO21

Slide handle for GridLine Type KO12	914226 KO12
Drawer Drawer front height 75 mm	927800 75
Drawer Drawer front height 100 mm	927800 100
Casing 24G with door hinged on the right / drawers Height / number of drawers 800/2	927610 800/2
Drawer casing 24G with drawers Height / number of drawers 800/7	927600 800/7
Worktop thickness 50 mm of beech marine ply Worktop length 2000 mm	926081 2000