

Garant GRIDLINE

Vario workbench with 2 drawer casings 24G, height 950 mm, Bamboo worktop, 20×20G, Worktop length: 2000/6+6mm



Order data

Order number	922811 2000/6+6
GTIN	4062406085643
Item class	9GG

Description

Version:

Workbench in sturdy steel construction. Drawer casing 24G can be locked centrally with cylinder lock. **100% full extension drawers** with differential runners and 75 kg load capacity.

Fitted with:

Drawer front height (left) mm: 75, 100, 100, 125, 150, 250

Drawer front height (right) mm: 75, 100, 100, 125, 150, 250

Supplied with:

2 × drawer casings, worktop.

Colour:

Casing body, support legs and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Note:

Supplied for self-assembly, saving freight costs. Delivered unassembled.

Technical description

Worktop length	2000 mm
Drawer body usable height	800 mm
Worktop thickness	50 mm
Series	vario
Drawer usable area in G	20×20

Number of drawers	12
Drawer usable depth in G	20
Drawer usable width	500 mm
Workbench/desk load capacity - maximum distributed load (on wood)	1000 kg
Worktop depth	750 mm
Drawer body depth	650 mm
Drawer usable depth	500 mm
Drawer body width	600 mm
Weight	220 kg
Drawer usable width in G	20
Height	950 mm
Material thickness	1 mm
Workbench height	950 mm
Drawer/pull-out shelf load capacity	75 kg
Insert thickness	50 mm
Drawer runner extension (partial/full extension)	100 %
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20x20G
Type of product	Workbench

Accessories

Drawer Drawer front height 75 mm	927800 75
Lock plate for GridLine Type KO21	914227 KO21
Drawer Drawer front height 150 mm	927800 150
Drawer Drawer front height 125 mm	927800 125

Drawer Drawer front height 250 mm	927800 250
Drawer Drawer front height 100 mm	927800 100
Drawer casing 24G with drawers Height / number of drawers 900/6	927600 900/6
Worktop thickness 50 mm of bamboo strips glued cross-wise Worktop length 2000 mm	926001 2000