

Garant GRIDLINE

**Vario workbench with 2 drawer casings 24G, height 850 mm, Eluplan worktop, dark, 20×20G, Worktop length: 2000/7+2Tmm****Order data**

|              |                  |
|--------------|------------------|
| Order number | 922807 2000/7+2T |
| GTIN         | 4062406085629    |
| Item class   | 9GG              |

**Description****Version:**

Workbench in sturdy steel construction. Drawer casing 24G can be locked centrally with cylinder lock. **100% full extension drawers** with differential runners and 75 kg load capacity.

**Fitted with:**

Drawer front height (left) mm: 75; 75; 75; 75; 100; 100; 200

Drawer front height (right) mm: 75#75

Door height (right) mm: 525

Number of height-adjustable storage shelves (right): 1

**Supplied with:**

2 × drawer casings, worktop.

**Colour:**

Casing body, support legs and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

**Note:**

Supplied for self-assembly, saving freight costs. Delivered unassembled.

**Technical description**

|   |         |
|---|---------|
| Workbench/desk load capacity - maximum distributed load (on wood) | 1000 kg |
| Drawer usable width   | 500 mm  |
| Height  | 850 mm  |

|  |  |
|--|--|
| Weight   | 185 kg   |
| Drawer usable area in G                          | 20×20  |
| Number of drawers                                | 9  |
| Series   | vario  |
| Drawer body depth                                | 650 mm   |
| Drawer body width                                | 600 mm   |
| Drawer usable depth                              | 500 mm   |
| Worktop depth                                    | 750 mm   |
| Worktop thickness                                | 50 mm  |
| Worktop length                                   | 2000 mm  |
| Drawer body usable height                        | 700 mm   |
| Drawer usable width in G                         | 20   |
| Drawer usable depth in G                         | 20   |
| Door opening angle                               | 180 degrees  |
| Material thickness                               | 1 mm   |
| Workbench height                                 | 850 mm   |
| Drawer/pull-out shelf load capacity              | 75 kg  |
| Insert thickness                                 | 50 mm  |
| Drawer runner extension (partial/full extension) | 100 %  |
| Cylinder lock                                    | modular lock barrel  |
| Colour selection                                 | RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003 |
| Product name attribute                           | 20×20G   |
| Type of product                                  | Workbench  |

## Accessories

|                                     |             |
|-------------------------------------|-------------|
| Drawer Drawer front height 200 mm   | 927800 200  |
| Slide handle for GridLine Type KO12 | 914226 KO12 |

|   |              |
|---|--------------|
| Drawer Drawer front height 100 mm   | 927800 100   |
| Drawer Drawer front height 75 mm  | 927800 75    |
| Lock plate for GridLine Type KO21   | 914227 KO21  |
| Drawer casing 24G with drawers Height / number of drawers 800/7                     | 927600 800/7 |
| Worktop with dark grey plastic coating (Eluplan) Worktop length 2000 mm             | 926241 2000  |
| Casing 24G with door hinged on the right / drawers Height / number of drawers 800/2 | 927610 800/2 |