

Garant GRIDLINE

Vario workbench with 2 drawer casings 24G, height 950 mm, Beech marine ply worktop, 20×20G, Worktop length: 2000/6+2Tmm



Order data

| | |
|--------------|------------------|
| Order number | 922814 2000/6+2T |
| GTIN | 4062406085698 |
| Item class | 9GG |

Description

Version:

Workbench in sturdy steel construction. Drawer casing 24G can be locked centrally with cylinder lock. **100% full extension drawers** with differential runners and 75 kg load capacity.

Fitted with:

Drawer front height (left) mm: 75, 100, 100, 125, 150, 250

Drawer front height (right) mm: 75#75

Door height (right) mm: 625

Number of height-adjustable storage shelves (right): 1

Supplied with:

2 × drawer casings, worktop.

Colour:

Casing body, support legs and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Note:

Supplied for self-assembly, saving freight costs. Delivered unassembled.

Technical description

| | |
|--------------------------|--------|
| Series | vario |
| Drawer body depth | 650 mm |
| Drawer usable width in G | 20 |

| | |
|---|--|
| Workbench/desk load capacity - maximum distributed load (on wood) | 1000 kg |
| Worktop thickness | 50 mm |
| Weight | 185 kg |
| Drawer usable area in G | 20×20 |
| Drawer usable width | 500 mm |
| Worktop length | 2000 mm |
| Drawer body usable height | 800 mm |
| Drawer usable depth in G | 20 |
| Drawer body width | 600 mm |
| Drawer usable depth | 500 mm |
| Number of drawers | 8 |
| Height | 950 mm |
| Worktop depth | 750 mm |
| Door opening angle | 180 degrees |
| Material thickness | 1 mm |
| Workbench height | 950 mm |
| Drawer/pull-out shelf load capacity | 75 kg |
| Insert thickness | 50 mm |
| Drawer runner extension (partial/full extension) | 100 % |
| Cylinder lock | modular lock barrel |
| Colour selection | RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003 |
| Product name attribute | 20×20G |
| Type of product | Workbench |

Accessories

| | |
|-----------------------------------|------------|
| Drawer Drawer front height 125 mm | 927800 125 |
|-----------------------------------|------------|

| | |
|--|--------------|
| Slide handle for GridLine Type KO12 | 914226 KO12 |
| Drawer Drawer front height 250 mm | 927800 250 |
| Drawer Drawer front height 100 mm | 927800 100 |
| Drawer Drawer front height 75 mm | 927800 75 |
| Drawer Drawer front height 150 mm | 927800 150 |
| Lock plate for GridLine Type KO21 | 914227 KO21 |
| Casing 24G with door hinged on the right / drawers Height / number of drawers 900/2 | 927610 900/2 |
| Worktop thickness 50 mm of beech marine ply Worktop length 2000 mm | 926081 2000 |
| Drawer casing 24G with drawers Height / number of drawers 900/6 | 927600 900/6 |