



Variable clamp with special jaw and 2 clamp handles, Jaw capacity: 1000mm



Order data

Order number	861750 1000
GTIN	4008158036366
Item class	83K

Description

Version:

Variable screw clamp – new flexibility with large spans up to 2 m! Beam of drawn profile steel, galvanised. End stops at each end can be removed without using tools. Slide jaw made of heat treatable steel, drop-forged. Wear-resistant smooth running steel spindle with trapezoidal thread and movable (up to 35°) special jaw anvil. Spindle tempered and burnished with adjustable clamp handle.

Application:

Modular principle gives many different application possibilities in woodworking and metalworking. The moving jaws can be replaced with other ones or also further ones added. The switch from clamping to spreading requires no tools. Clamp can also be inserted through an opening in the workpiece. Central positioning on the workpiece prevents tipping. The movable special jaw anvil permits clamping diagonal workpieces up to 35°. **Maximum clamping pressure up to approx. 6500 N.**

Note:

See spare parts list for No. 861756 (clamping handle), 861757 (wooden handle) or 861758 (lever handle) for spare sliding jaws.

Technical description

Throat	120 mm
Jaw capacity	1000 mm
Weight	4.78 kg
Cross section of the slide rail	27×13 mm
Type of product	Clamp

Accessories

Moving jaw with wooden handle	861757
Moving jaw with tommy bar	861756
Moving jaw with lever handle	861758