

Garant GRIDLINE

**Vario workbench with 2 drawer casings 24G, height 950 mm, Eluplan worktop, dark, 20×20G, Worktop length: 2000/6+2Tmm****Order data**

Order number	922817 2000/6+2T
GTIN	4062406085735
Item class	9GG

**Description****Version:**

Workbench in sturdy steel construction. Drawer casing 24G can be locked centrally with cylinder lock. **100% full extension drawers** with differential runners and 75 kg load capacity.

**Fitted with:**

Drawer front height (left) mm: 75, 100, 100, 125, 150, 250

Drawer front height (right) mm: 75, 75

Door height (right) mm: 625

Number of height-adjustable storage shelves (right): 1

**Supplied with:**

2 × drawer casings, worktop.

**Colour:**

Casing body, support legs and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

**Note:**

Supplied for self-assembly, saving freight costs. Delivered unassembled.

**Technical description**

Worktop depth	750 mm
Height	950 mm
Worktop thickness	50 mm

Weight	185 kg
Number of drawers	8
Drawer body width	600 mm
Drawer body usable height	800 mm
Worktop length	2000 mm
Workbench/desk load capacity - maximum distributed load (on wood)	1000 kg
Drawer usable depth in G	20
Drawer usable width in G	20
Series	vario
Drawer usable area in G	20×20
Drawer body depth	650 mm
Drawer usable width	500 mm
Drawer usable depth	500 mm
Door opening angle	180 degrees
Material thickness	1 mm
Workbench height	950 mm
Drawer/pull-out shelf load capacity	75 kg
Insert thickness	50 mm
Drawer runner extension (partial/full extension)	100 %
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20×20G
Type of product	Workbench

## Accessories

Drawer Drawer front height 250 mm	927800 250
-----------------------------------	------------

Drawer Drawer front height 150 mm	927800 150
Drawer Drawer front height 125 mm	927800 125
Slide handle for GridLine Type KO12	914226 KO12
Drawer Drawer front height 75 mm	927800 75
Lock plate for GridLine Type KO21	914227 KO21
Drawer Drawer front height 100 mm	927800 100
Worktop with dark grey plastic coating (Eluplan) Worktop length 2000 mm	926241 2000
Casing 24G with door hinged on the right / drawers Height / number of drawers 900/2	927610 900/2
Drawer casing 24G with drawers Height / number of drawers 900/6	927600 900/6