

Garant GRIDLINE

Vario workbench with 2 drawer casings, swing-away and height adjustment unit, height 850 mm, Bamboo worktop, 20×20G, Worktop length: 1500/6+1Tmm



Order data

Order number	922821 1500/6+1T
GTIN	4062406085759
Item class	9GG

Description

Version:

Workbench in sturdy steel construction. Casing with GARANT swing away and height adjustment unit No. 967568 size 120, including vice No. 967100 size 120. Vice casing width 16G, including a drawer. Drawer casing 24G can be locked centrally with cylinder lock. **100% full extension drawers** with differential runners and 75 kg load capacity. Casing with vice: Cupboard lockable with a cylinder lock. Drawer not lockable.

Fitted with:

Drawer front height (left) mm: 50, 75, 100, 125, 150, 200

Drawer front height (right) mm: 150

Door height (right) mm: 575

Supplied with:

1 × casing with drawers, 1 × casing including a swing away and height adjustment unit with vice, worktop.

Optional extras:

Additional accessories such as manual height adjustment, wheels, side panels, etc. can be found under GridLine individual components in Group 92.

Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Note:

Supplied for self-assembly, saving freight costs. Delivered unassembled.

Technical description

Number of drawers	7
Worktop thickness	50 mm
Drawer body height	800 mm
Drawer usable depth	500 mm
Drawer body usable height	700 mm
Worktop depth	750 mm
Drawer usable depth in G	20
Height	850 mm
Weight	179 kg
Worktop length	1500 mm
Drawer usable width in G	20
Drawer usable area in G	20×20
Drawer usable width	500 mm
Workbench/desk load capacity - maximum distributed load (on wood)	1000 kg
Series	vario
Drawer body width	600 mm
Drawer body depth	650 mm
Material thickness	1 mm
Workbench height	850 mm
Drawer/pull-out shelf load capacity	75 kg
Insert thickness	50 mm
Drawer runner extension (partial/full extension)	100 %
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20×20G
Type of product	Workbench

Accessories

Drawer Drawer front height 200 mm	927800 200
Drawer Drawer front height 100 mm	927800 100
Drawer Drawer front height 75 mm	927800 75
Lock plate for GridLine Type KO21	914227 KO21
Drawer Drawer front height 150 mm	927800 150
Drawer Drawer front height 150 mm	927500 150
Drawer Drawer front height 125 mm	927800 125
Drawer Drawer front height 50 mm	927800 50
Worktop thickness 50 mm of bamboo strips glued cross-wise Worktop length 1500 mm	926001 1500
Drawer casing 24G with drawers Height / number of drawers 800/6	927600 800/6
16G cabinet casing suitable for swing away and height adjustment unit and vice Height 800 mm	927321 800