

Garant GRIDLINE

Vario workbench with 2 drawer casings, swing-away and height adjustment unit, height 950 mm, Beech marine ply worktop, 20×20G, Worktop length: 1500/6+1Tmm



Order data

| | |
|--------------|------------------|
| Order number | 922834 1500/6+1T |
| GTIN | 4062406085933 |
| Item class | 9GG |

Description

Version:

Workbench in sturdy steel construction. Casing with GARANT swing away and height adjustment unit No. 967568 size 120, including vice No. 967100 size 120. Vice casing width 16G, including a drawer. Drawer casing 24G can be locked centrally with cylinder lock. **100% full extension drawers** with differential runners and 75 kg load capacity. Casing with vice: Cupboard lockable with a cylinder lock. Drawer not lockable.

Fitted with:

Drawer front height (left) mm: 75, 100, 100, 125, 150, 250

Drawer front height (right) mm: 150

Door height (right) mm: 675

Supplied with:

1 × casing with drawers, 1 × casing including a swing away and height adjustment unit with vice, worktop.

Optional extras:

Additional accessories such as manual height adjustment, wheels, side panels, etc. can be found under GridLine individual components in Group 92.

Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Note:

Supplied for self-assembly, saving freight costs. Delivered unassembled.

Technical description

| | |
|---|--|
| Drawer usable depth | 500 mm |
| Drawer usable depth in G | 20 |
| Workbench/desk load capacity - maximum distributed load (on wood) | 1000 kg |
| Drawer body depth | 650 mm |
| Drawer usable width in G | 20 |
| Worktop depth | 750 mm |
| Worktop thickness | 50 mm |
| Drawer body height | 900 mm |
| Drawer body width | 600 mm |
| Drawer usable width | 500 mm |
| Worktop length | 1500 mm |
| Series | vario |
| Number of drawers | 7 |
| Drawer usable area in G | 20×20 |
| Weight | 186 kg |
| Drawer body usable height | 800 mm |
| Height | 950 mm |
| Material thickness | 1 mm |
| Workbench height | 950 mm |
| Drawer/pull-out shelf load capacity | 75 kg |
| Insert thickness | 50 mm |
| Drawer runner extension (partial/full extension) | 100 % |
| Cylinder lock | modular lock barrel |
| Colour selection | RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003 |
| Product name attribute | 20×20G |

Type of product

Workbench

Accessories

| | |
|--|--------------|
| Drawer Drawer front height 100 mm | 927800 100 |
| Drawer Drawer front height 75 mm | 927800 75 |
| Drawer Drawer front height 250 mm | 927800 250 |
| Drawer Drawer front height 150 mm | 927500 150 |
| Lock plate for GridLine Type KO21 | 914227 KO21 |
| Drawer Drawer front height 150 mm | 927800 150 |
| Drawer Drawer front height 125 mm | 927800 125 |
| Worktop thickness 50 mm of beech marine ply Worktop length 1500 mm | 926081 1500 |
| 16G cabinet casing suitable for swing away and height adjustment unit and vice Height 900 mm | 927321 900 |
| Drawer casing 24G with drawers Height / number of drawers 900/6 | 927600 900/6 |