

Garant GRIDLINE

## Workbench with undercarriage, height 850 mm with Eluplan worktop, dark, 20×20G, Worktop length: 1500 mm



### Order data

Order number	923617 1500
GTIN	4062406085995
Item class	9GG

### Description

#### IMPORTANT: item is configurable

#### Version:

Workbench in sturdy steel construction with frame of rectangular hollow section, **100% full extension drawers** with differential runners and 75 kg load capacity. **Individual drawer release system** prevents the opening of drawers during transport. Mobile base is fitted with 2 castors and 2 fixed wheels Ø100 mm with solid rubber tyres. The bench is evenly raised or lowered. This combines high stability at the point of use with the ease of transport. Mobile base load capacity up to **400 kg** (workbench incl. contents). Feet with plastic pads, do not damage the floor. Drawer casing 24G can be locked centrally with cylinder lock.

#### Fitted with:

Drawer front height (right) mm: 75, 100, 150, 200

Drawer front height (right): 1

#### Colour:

Casing body, support legs and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **wheels and push handle always RAL 7016 anthracite** (not configurable), **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Individual drawer release system: One-hand

Drawer usable area in G: 20×20

Height: 850 mm

Worktop length: 1500 mm

Worktop depth: 750 mm

Worktop thickness: 50 mm

Support cabinet width: 1300 mm

Support cabinet depth: 700 mm

## Technical description

ComfortClose	no
Drawer usable width in G	20
Push handle	no
Worktop depth	750 mm
Number of height-adjustable shelves	1
Bumper	no
Castor Ø	100 mm
Drawer usable width	500 mm
Drawer usable depth	500 mm
Fixed wheel Ø	100 mm
Worktop thickness	50 mm
Support cabinet depth	700 mm
Height	850 mm
Material of wheel	Solid rubber
Surface worktop	clear varnished
Material of worktop	Beech marine ply
Number of drawers	4
Number of fixed wheels without parking brake	2
can be lowered	yes
Number of castors without parking brake	2
maximum load capacity, mobile unit	400 kg
Weight	151.6 kg
Drawer usable depth in G	20
Drawer usable area in G	20×20
Drawer body usable height	525 mm
Support cabinet width	1300 mm

Worktop length	1500 mm
Individual drawer release system	One-hand
Plug type, input	F
Nominal voltage	250 V
Design version	Steel hollow section construction
Material thickness	1 mm
Workbench height	850 mm
Drawer/pull-out shelf load capacity	75 kg
Workbench/desk load capacity - maximum distributed load (on wood)	400 kg
Insert thickness	50 mm
Drawer runner extension (partial/full extension)	100 %
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Safety certificate	GS TÜV Süd
Product name attribute	20x20G
Type of product	Workbench mobile

## Accessories

Mat for drawers Dimension in G 20X20	951830 20X20
Workshop set Number of tools 26	955081 26
Marking out and sawing Number of tools 8	954895 8
Ribbed rubber mat for drawers Dimension in G 20X20	951910 20X20
Slotted dividers / plain dividers set Drawer front height / type 100/2	950320 100/2
Combination spanner set Number of tools 20	952505 20
easyPick small parts storage bins set Drawer front height / type 75/3	950300 75/3

File set Number of tools 6	952253 6
Slotted dividers / plain dividers set Drawer front height / type 75/2	950320 75/2
Slotted dividers / plain dividers set Drawer front height / type 100/1	950320 100/1
Drawer with one-hand individual drawer release system Drawer front height 200 mm	927805 200
easyPick small parts storage bins set Drawer front height / type 75/1	950300 75/1
Pliers set Number of tools 5	954305 5
Drawer with one-hand individual drawer release system Drawer front height 150 mm	927805 150
Pliers set Number of tools 5	954295 5
Socket set 1/2 inch Number of tools 32	953821 32
Socket set 1/4 inch and 1/2 inch Number of tools 39	953833 39
Workshop set Number of tools 22	955071 22
Slotted dividers / plain dividers set Drawer front height / type 150/5	950320 150/5
Hammer set Number of tools 3	954690 3
Screwdriver set Number of tools 10	953521 10
Slotted dividers / plain dividers set Drawer front height / type 150/4	950320 150/4
Slotted dividers / plain dividers set Drawer front height / type 75/3	950320 75/3
Drawer with one-hand individual drawer release system Drawer front height 100 mm	927805 100
Non-slip mats set for drawers, 5 pieces Dimension in G 20X20	951885 20X20
Lock plate for GridLine Type KO21	914227 KO21
Drawer with one-hand individual drawer release system Drawer front height 75 mm	927805 75
Slotted dividers / plain dividers set Drawer front height / type 75/1	950320 75/1

Socket set 1/4 inch and 1/2 inch Number of tools 37	953828 37
Slotted dividers / plain dividers set Drawer front height / type 100/3	950320 100/3
easyPick small parts storage bins set Drawer front height / type 75/2	950300 75/2