

Garant GRIDLINE

**Workbench with undercarriage, height 850 mm with bamboo worktop, 20×20G, Worktop length: 1500mm****Order data**

|              |               |
|--------------|---------------|
| Order number | 923651 1500   |
| GTIN         | 4062406086008 |
| Item class   | 9GG           |

**Description****Version:**

Workbench in sturdy steel construction with frame of rectangular hollow section, **100% full extension drawers** with differential runners and 75 kg load capacity. **Individual drawer release system** prevents the opening of drawers during transport. Undercarriage is fitted with 2 castors and 2 fixed wheels Ø100 mm with solid rubber tyres. The bench is evenly raised or lowered using the 2-component Haptoprene® lifting handle. This combines high stability at the point of use with the ease of transport. Undercarriage load capacity up to **400 kg** (workbench incl. contents). Feet with plastic pads, do not damage the floor. Drawer casing 24G can be locked centrally with cylinder lock.

**Fitted with:**

Drawer front height each side mm: 75

Door height each side mm: 425

**Colour:**

Casing body, support legs and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **wheels and push handle always RAL 7016 anthracite** (not configurable), **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

**Technical description**

|                          |        |
|--------------------------|--------|
| Drawer usable depth in G | 20     |
| Worktop depth            | 750 mm |

|  |                                   |
|--|-----------------------------------|
| Bumper                                       | no                                |
| Drawer usable width in G                     | 20                                |
| can be lowered                               | yes                               |
| Fixed wheel Ø                                | 100 mm                            |
| Surface worktop                              | clear varnished                   |
| Drawer usable area in G                      | 20×20                             |
| Support cabinet depth                        | 700 mm                            |
| Support cabinet width                        | 1300 mm                           |
| Material of worktop                          | Bamboo                            |
| Number of castors without parking brake      | 2                                 |
| Number of doors                              | 2                                 |
| ComfortClose                                 | no                                |
| Drawer body usable height                    | 525 mm                            |
| Number of fixed wheels without parking brake | 2                                 |
| Push handle                                  | no                                |
| Worktop thickness                            | 50 mm                             |
| Height                                       | 850 mm                            |
| Number of drawers                            | 2                                 |
| Drawer usable width                          | 500 mm                            |
| Castor Ø                                     | 100 mm                            |
| Material of wheel                            | Solid rubber                      |
| Worktop length                               | 1500 mm                           |
| Drawer usable depth                          | 500 mm                            |
| Weight                                       | 139.6 kg                          |
| maximum load capacity, mobile unit           | 400 kg                            |
| Individual drawer release system             | One-hand                          |
| Plug type, input                             | F                                 |
| Nominal voltage                              | 250 V                             |
| Design version                               | Steel hollow section construction |

|   |  |
|---|--|
| Material thickness  | 1 mm   |
| Workbench height  | 850 mm   |
| Drawer/pull-out shelf load capacity                               | 75 kg  |
| Workbench/desk load capacity - maximum distributed load (on wood) | 400 kg   |
| Insert thickness  | 50 mm  |
| Drawer runner extension (partial/full extension)                  | 100 %  |
| Door opening angle  | 180 degrees  |
| Cylinder lock   | modular barrel   |
| Colour selection  | RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003 |
| Product name attribute  | 20x20G   |
| Type of product   | mobile workbench   |

## Accessories

|  |             |
|--|-------------|
| Drawer with one-handed individual drawer release system<br>Drawer front height 75 mm | 927805 75   |
| Lock plate for GridLine Type KO21  | 914227 KO21 |
| Slide handle for GridLine Type KO12  | 914226 KO12 |