

Garant GRIDLINE

Workbench with undercarriage, height 950 mm with beech marine ply worktop, 20×20G, Worktop length: 1500 mm



Order data

Order number	923674 1500
GTIN	4062406086114
Item class	9GG

Description

IMPORTANT: item is configurable

Version:

Workbench in sturdy steel construction with frame of rectangular hollow section, **100% full extension drawers** with differential runners and 75 kg load capacity. **Individual drawer release system** prevents the opening of drawers during transport. Undercarriage is fitted with 2 castors and 2 fixed wheels Ø100 mm with solid rubber tyres. The bench is evenly raised or lowered using the 2-component Haptoprene® lifting handle. This combines high stability at the point of use with the ease of transport. Undercarriage load capacity up to **400 kg** (workbench incl. contents). Feet with plastic pads, do not damage the floor. Drawer casing 24G can be locked centrally with cylinder lock.

Fitted with:

Drawer front height each side mm: 75

Door height each side mm: 525

Number of height-adjustable storage shelves: 2

Colour:

Casing body, support legs and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **wheels and push handle always RAL 7016 anthracite** (not configurable), **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Individual drawer release system: One-hand

Drawer usable area in G: 20×20

Height: 950 mm

Worktop length: 1500 mm

Worktop depth: 750 mm

Worktop thickness: 50 mm
 Support cabinet width: 1300 mm
 Support cabinet depth: 700 mm

Technical description

Material of wheel	Solid rubber
ComfortClose	no
Support cabinet width	1300 mm
Drawer usable width	500 mm
Drawer usable depth	500 mm
Height	950 mm
Surface worktop	clear varnished
Number of castors without parking brake	2
Drawer usable width in G	20
Drawer usable depth in G	20
Material of worktop	Beech marine ply
Push handle	no
maximum load capacity, mobile unit	400 kg
Castor Ø	100 mm
Number of doors	2
Worktop depth	750 mm
Drawer usable area in G	20×20
Support cabinet depth	700 mm
Fixed wheel Ø	100 mm
Number of drawers	2
Weight	155 kg
Worktop thickness	50 mm
Worktop length	1500 mm
Bumper	no
Number of fixed wheels without parking brake	2

Drawer body usable height	625 mm
can be lowered	yes
Individual drawer release system	One-hand
Nominal voltage	250 V
Plug type, input	F
Design version	Steel hollow section construction
Material thickness	1 mm
Workbench height	950 mm
Drawer/pull-out shelf load capacity	75 kg
Workbench/desk load capacity - maximum distributed load (on wood)	400 kg
Insert thickness	50 mm
Drawer runner extension (partial/full extension)	100 %
Door opening angle	180 degrees
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20x20G
Type of product	Workbench mobile

Accessories

Slide handle for GridLine Type KO12	914226 KO12
Lock plate for GridLine Type KO21	914227 KO21
Socket set 1/4 inch and 1/2 inch Number of tools 37	953828 37
Socket set 1/4 inch and 1/2 inch Number of tools 39	953833 39
File set Number of tools 6	952253 6
Slotted dividers / plain dividers set Drawer front height / type 75/3	950320 75/3
Socket set 1/2 inch Number of tools 32	953821 32

easyPick small parts storage bins set Drawer front height / type 75/1	950300 75/1
easyPick small parts storage bins set Drawer front height / type 75/2	950300 75/2
Pliers set Number of tools 5	954295 5
Non-slip mats set for drawers, 5 pieces Dimension in G 20X20	951885 20X20
Screwdriver set Number of tools 10	953521 10
Pliers set Number of tools 5	954305 5
Mat for drawers Dimension in G 20X20	951830 20X20
Marking out and sawing Number of tools 8	954895 8
Drawer with one-hand individual drawer release system Drawer front height 75 mm	927805 75
Hammer set Number of tools 3	954690 3
easyPick small parts storage bins set Drawer front height / type 75/3	950300 75/3
Slotted dividers / plain dividers set Drawer front height / type 75/1	950320 75/1
Slotted dividers / plain dividers set Drawer front height / type 75/2	950320 75/2
Ribbed rubber mat for drawers Dimension in G 20X20	951910 20X20