

Garant GRIDLINE

Workbench with undercarriage, with height adjuster and vice, with beech marine ply worktop, 20×20G, Worktop length: 1250mm**Order data**

Order number	923694 1250
GTIN	4062406086190
Item class	9GG

Description**Version:**

Workbench in sturdy steel construction with frame of rectangular hollow section. **100% full extension drawers** with differential runners and 75 kg load capacity. **Individual drawer release system** prevents the opening of drawers during transport. Undercarriage is fitted with 2 castors and 2 fixed wheels Ø100 mm with solid rubber tyres. The bench is evenly raised or lowered using the 2-component Haptoprene® lifting handle. This combines high stability at the point of use with the ease of transport. Undercarriage load capacity up to **400 kg** (workbench incl. contents). Feet with plastic pads, do not damage the floor. Lockable with cylinder lock.

Fitted with:

Drawer front height, mm: 75

Door height, mm: 425

Door height, vice body, mm: 575

Supplied with:

Supplied with GARANT swing away and height adjustment unit No. 967568 size 120 and GARANT vice No. 967100 size 120.

Colour:

Casing body, support legs and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **wheels and push handle always RAL 7016 anthracite** (not configurable), **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Technical description

Drawer usable width	500 mm
Push handle	no
Number of castors without parking brake	2
Material of wheel	Solid rubber
Weight	142.3 kg
maximum load capacity, mobile unit	400 kg
Height	850 mm
can be lowered	yes
Bumper	no
Fixed wheel Ø	100 mm
Drawer usable width in G	20
ComfortClose	no
Number of doors	2
Worktop thickness	50 mm
Drawer usable depth in G	20
Drawer usable depth	500 mm
Worktop depth	750 mm
Castor Ø	100 mm
Number of fixed wheels without parking brake	2
Drawer usable area in G	20×20
Surface worktop	clear varnished
Number of drawers	1
Material of worktop	Beech marine ply
Worktop length	1250 mm
Individual drawer release system	One-hand
Design version	Steel hollow section construction
Material thickness	1 mm
Workbench height	850 mm
Drawer/pull-out shelf load capacity	75 kg

Workbench/desk load capacity - maximum distributed load (on wood)	400 kg
Insert thickness	50 mm
Drawer runner extension (partial/full extension)	100 %
Door opening angle	180 degrees
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20x20G
Type of product	mobile workbench

Accessories

Slide handle for GridLine Type KO12	914226 KO12
Lock plate for GridLine Type KO21	914227 KO21
Drawer with one-handed individual drawer release system Drawer front height 75 mm	927805 75