

Garant GRIDLINE

Workbench with undercarriage, with height adjuster and vice, with Eluplan worktop, dark, 20×20G, Worktop length: 1250 mm



Order data

Order number	923697 1250
GTIN	4062406086206
Item class	9GG

Description

IMPORTANT: item is configurable

Version:

Workbench in sturdy steel construction with frame of rectangular hollow section. **100% full extension drawers** with differential runners and 75 kg load capacity. **Individual drawer release system** prevents the opening of drawers during transport. Undercarriage is fitted with 2 castors and 2 fixed wheels Ø100 mm with solid rubber tyres. The bench is evenly raised or lowered using the 2-component Haptoprene® lifting handle. This combines high stability at the point of use with the ease of transport. Undercarriage load capacity up to **400 kg** (workbench incl. contents). Feet with plastic pads, do not damage the floor. Lockable with cylinder lock.

Fitted with:

Drawer front height, mm: 75

Door height, mm: 425

Door height, vice body, mm: 575

Supplied with:

Supplied with GARANT swing away and height adjustment unit No. 967568 size 120 and GARANT vice No. 967100 size 120.

Colour:

Casing body, support legs and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **wheels and push handle always RAL 7016 anthracite** (not configurable), **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Individual drawer release system: One-hand

Drawer usable area in G: 20×20

Height: 850 mm
 Worktop length: 1250 mm
 Worktop depth: 750 mm
 Worktop thickness: 50 mm
 Drawer usable width: 500 mm
 Drawer usable depth: 500 mm

Technical description

Number of drawers	1
Number of castors without parking brake	2
Castor Ø	100 mm
Drawer usable depth in G	20
Worktop length	1250 mm
Number of doors	1
Drawer usable width in G	20
Material of worktop	Eluplan worktop, dark
Bumper	no
Number of fixed wheels without parking brake	2
Drawer usable depth	500 mm
Push handle	no
Worktop thickness	50 mm
ComfortClose	no
Drawer usable width	500 mm
Worktop depth	750 mm
maximum load capacity, mobile unit	400 kg
Fixed wheel Ø	100 mm
Height	850 mm
Drawer usable area in G	20×20
can be lowered	yes
Material of wheel	Solid rubber
Weight	130.7 kg

Individual drawer release system	One-hand
Plug type, input	F
Nominal voltage	250 V
Design version	Steel hollow section construction
Material thickness	1 mm
Workbench height	850 mm
Drawer/pull-out shelf load capacity	75 kg
Workbench/desk load capacity - maximum distributed load (on wood)	400 kg
Insert thickness	50 mm
Drawer runner extension (partial/full extension)	100 %
Door opening angle	180 degrees
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20x20G
Type of product	Workbench mobile

Accessories

Drawer with one-hand individual drawer release system Drawer front height 75 mm	927805 75
easyPick small parts storage bins set Drawer front height / type 75/3	950300 75/3
Socket set 1/4 inch and 1/2 inch Number of tools 39	953833 39
Marking out and sawing Number of tools 8	954895 8
File set Number of tools 6	952253 6
Slotted dividers / plain dividers set Drawer front height / type 75/1	950320 75/1
easyPick small parts storage bins set Drawer front height / type 75/2	950300 75/2

Lock plate for GridLine Type HU21	914227 HU21
Slide handle for GridLine Type KO12	914226 KO12
Pliers set Number of tools 5	954305 5
Slotted dividers / plain dividers set Drawer front height / type 75/2	950320 75/2
Socket set 1/4 inch and 1/2 inch Number of tools 37	953828 37
Hammer set Number of tools 3	954690 3
Screwdriver set Number of tools 10	953521 10
Ribbed rubber mat for drawers Dimension in G 20X20	951910 20X20
Slotted dividers / plain dividers set Drawer front height / type 75/3	950320 75/3
Pliers set Number of tools 5	954295 5
Non-slip mats set for drawers, 5 pieces Dimension in G 20X20	951885 20X20
easyPick small parts storage bins set Drawer front height / type 75/1	950300 75/1
Mat for drawers Dimension in G 20X20	951830 20X20
Socket set 1/2 inch Number of tools 32	953821 32