

Garant GRIDLINE

Workbench with undercarriage, with height adjuster and vice, with beech marine ply worktop, 20×20G, Worktop length: 1250mm**Order data**

Order number	923714 1250
GTIN	4062406086220
Item class	9GG

Description**Version:**

Workbench in sturdy steel construction with frame of rectangular hollow section. **100% full extension drawers** with differential runners and 75 kg load capacity. **Individual drawer release system** prevents the opening of drawers during transport. Undercarriage is fitted with 2 castors and 2 fixed wheels Ø100 mm with solid rubber tyres. The bench is evenly raised or lowered using the 2-component Haptoprene® lifting handle. This combines high stability at the point of use with the ease of transport. Undercarriage load capacity up to **400 kg** (workbench incl. contents). Feet with plastic pads, do not damage the floor. Lockable with cylinder lock.

Fitted with:

Drawer front height, mm: 75

Door height, mm: 525

Door height, vice body, mm: 675

Number of height-adjustable storage shelves: 1

Supplied with:

Supplied with GARANT swing away and height adjustment unit No. 967568 size 120 and GARANT vice No. 967100 size 120.

Colour:

Casing body, support legs and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **wheels and push handle always RAL 7016 anthracite** (not configurable), **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Technical description

Number of doors	2
Material of wheel	Solid rubber
Height	950 mm
Push handle	no
Drawer usable depth	500 mm
Material of worktop	Beech marine ply
Surface worktop	clear varnished
Drawer usable area in G	20×20
Fixed wheel Ø	100 mm
Drawer usable depth in G	20
Drawer usable width	500 mm
can be lowered	yes
Castor Ø	100 mm
Worktop thickness	50 mm
Number of fixed wheels without parking brake	2
Number of castors without parking brake	2
Weight	149.2 kg
Number of drawers	1
maximum load capacity, mobile unit	400 kg
Bumper	no
Drawer usable width in G	20
Worktop length	1250 mm
Worktop depth	750 mm
ComfortClose	no
Individual drawer release system	One-hand
Design version	Steel hollow section construction
Material thickness	1 mm
Workbench height	950 mm

Drawer/pull-out shelf load capacity	75 kg
Workbench/desk load capacity - maximum distributed load (on wood)	400 kg
Insert thickness	50 mm
Drawer runner extension (partial/full extension)	100 %
Door opening angle	180 degrees
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20×20G
Type of product	mobile workbench

Accessories

Lock plate for GridLine Type HU21	914227 HU21
Slide handle for GridLine Type KO12	914226 KO12
Drawer with one-handed individual drawer release system Drawer front height 75 mm	927805 75