

Garant GRIDLINE

**Workbench with undercarriage, without height adjuster and vice, with Eluplan worktop, dark, 20×20G, Worktop length: 1250mm****Order data**

Order number	923737 1250
GTIN	4062406086268
Item class	9GG

**Description****Version:**

Workbench in sturdy steel construction with frame of rectangular hollow section. **100% full extension drawers** with differential runners and 75 kg load capacity. **Individual drawer release system** prevents the opening of drawers during transport. Undercarriage is fitted with 2 castors and 2 fixed wheels Ø100 mm with solid rubber tyres. The bench is evenly raised or lowered using the 2-component Haptoprene® lifting handle. This combines high stability at the point of use with the ease of transport. Undercarriage load capacity up to **400 kg** (workbench incl. contents). Feet with plastic pads, do not damage the floor. Lockable with cylinder lock.

**Fitted with:**

Drawer front height, mm: 75

Door height, mm: 425

Door height, vice body, mm: 575

**Colour:**

Casing body, support legs and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **wheels and push handle always RAL 7016 anthracite** (not configurable), **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

**Technical description**

Material of worktop	Eluplan worktop, dark
can be lowered	yes

Number of fixed wheels without parking brake	2
Castor Ø	100 mm
Worktop thickness	50 mm
Worktop length	1250 mm
Weight	111.1 kg
Worktop depth	750 mm
Drawer usable width	500 mm
Drawer usable depth in G	20
Drawer usable depth	500 mm
maximum load capacity, mobile unit	400 kg
Height	850 mm
Number of doors	2
Number of castors without parking brake	2
Number of drawers	1
ComfortClose	no
Fixed wheel Ø	100 mm
Drawer usable area in G	20×20
Drawer usable width in G	20
Material of wheel	Solid rubber
Push handle	no
Bumper	no
Individual drawer release system	One-hand
Design version	Steel hollow section construction
Material thickness	1 mm
Workbench height	850 mm
Drawer/pull-out shelf load capacity	75 kg
Workbench/desk load capacity - maximum distributed load (on wood)	400 kg
Insert thickness	50 mm
Drawer runner extension (partial/full extension)	100 %

Door opening angle	180 degrees
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20×20G
Type of product	mobile workbench

---

## Accessories

Lock plate for GridLine Type HU21	914227 HU21
Slide handle for GridLine Type KO12	914226 KO12
Drawer with one-handed individual drawer release system Drawer front height 75 mm	927805 75