

Garant GRIDLINE

Workbench with undercarriage, without height adjuster and vice, with beech marine ply worktop, 20×20G, Worktop length: 1250mm**Order data**

Order number	923754 1250
GTIN	4062406086282
Item class	9GG

Description**Version:**

Workbench in sturdy steel construction with frame of rectangular hollow section. **100% full extension drawers** with differential runners and 75 kg load capacity. **Individual drawer release system** prevents the opening of drawers during transport. Undercarriage is fitted with 2 castors and 2 fixed wheels Ø100 mm with solid rubber tyres. The workbench is evenly raised or lowered using the 2-component Haptoprene lifting handle. This combines high stability at the point of use with ease of transport. Undercarriage load capacity up to **400 kg** (workbench incl. contents). Feet with plastic pads, do not damage the floor. Lockable with cylinder lock.

Fitted with:

Drawer front height, mm: 75

Door height, mm: 525

Door height, vice body, mm: 675

Number of height-adjustable storage shelves: 1

Colour:

Casing body, support legs and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **wheels and push handle always RAL 7016 anthracite** (not configurable), **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Technical description

Surface worktop	clear varnished
-----------------	-----------------

Data sheet

Drawer usable area in G	20×20
ComfortClose	no
Worktop thickness	50 mm
Number of doors	2
Material of wheel	Solid rubber
Drawer usable width	500 mm
Bumper	no
Fixed wheel Ø	100 mm
Push handle	no
Castor Ø	100 mm
Number of castors without parking brake	2
Drawer usable depth in G	20
can be lowered	yes
Number of fixed wheels without parking brake	2
Drawer usable depth	500 mm
Worktop depth	750 mm
Drawer usable width in G	20
maximum load capacity, mobile unit	400 kg
Height	950 mm
Weight	129.6 kg
Number of drawers	1
Worktop length	1250 mm
Material of worktop	Beech marine ply
Individual drawer release system	One-hand
Design version	Steel hollow section construction
Material thickness	1 mm
Workbench height	950 mm
Drawer/pull-out shelf load capacity	75 kg
Workbench/desk load capacity - maximum distributed load (on wood)	400 kg

Data sheet

Insert thickness	50 mm
Drawer runner extension (partial/full extension)	100 %
Door opening angle	180 degrees
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20x20G
Type of product	mobile workbench

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/923754-1250>