

Garant GRIDLINE

Workbench with undercarriage, without height adjuster and vice, with bamboo worktop, 20×20G, Worktop length: 1250mm



Order data

Order number	923731 1250
GTIN	4062406086244
Item class	9GG

Description

Version:

Workbench in sturdy steel construction with frame of rectangular hollow section. **100% full extension drawers** with differential runners and 75 kg load capacity. **Individual drawer release system** prevents the opening of drawers during transport. Undercarriage is fitted with 2 castors and 2 fixed wheels Ø100 mm with solid rubber tyres. The bench is evenly raised or lowered using the 2-component Haptoprene® lifting handle. This combines high stability at the point of use with the ease of transport. Undercarriage load capacity up to **400 kg** (workbench incl. contents). Feet with plastic pads, do not damage the floor. Lockable with cylinder lock.

Fitted with:

Drawer front height, mm: 75

Door height, mm: 425

Door height, vice body, mm: 575

Colour:

Casing body, support legs and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **wheels and push handle always RAL 7016 anthracite** (not configurable), **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Technical description

Weight	117 kg
maximum load capacity, mobile unit	400 kg

Material of wheel	Solid rubber
Worktop thickness	50 mm
Drawer usable width in G	20
Number of fixed wheels without parking brake	2
Height	850 mm
can be lowered	yes
Number of castors without parking brake	2
ComfortClose	no
Drawer usable depth in G	20
Castor Ø	100 mm
Number of doors	2
Drawer usable width	500 mm
Drawer usable area in G	20×20
Fixed wheel Ø	100 mm
Material of worktop	Bamboo worktop
Worktop length	1250 mm
Push handle	no
Worktop depth	750 mm
Number of drawers	1
Bumper	no
Drawer usable depth	500 mm
Individual drawer release system	One-hand
Design version	Steel hollow section construction
Material thickness	1 mm
Workbench height	850 mm
Drawer/pull-out shelf load capacity	75 kg
Workbench/desk load capacity - maximum distributed load (on wood)	400 kg
Insert thickness	50 mm
Drawer runner extension (partial/full extension)	100 %

Door opening angle	180 degrees
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20x20G
Type of product	mobile workbench

Accessories

Drawer with one-handed individual drawer release system Drawer front height 75 mm	927805 75
Slide handle for GridLine Type KO12	914226 KO12
Lock plate for GridLine Type HU21	914227 HU21