

Garant GRIDLINE

Workbench, left side open, right side 4 drawers, Beech marine ply worktop, 20x20G, Worktop length: 1500mm



Order data

Order number	921004 1500
GTIN	4062406086305
Item class	9GG

Description

Version:

Workbench in sturdy steel construction with frame of rectangular hollow section. Drawer cabinet can be locked centrally with cylinder lock. **100% full extension drawers** with differential runners and 75 kg load capacity. Feet with plastic pads, do not damage the floor.

Drawer bodies always RAL 7035 light grey, **powder coated**. Variable colours for the drawer fronts. No surrounding ledges, thereby allowing optimum cleaning and full availability of the area for drawer dividers (boxes, rigid foam inlays, slotted partitions). Drawer runner mountings at 25 mm intervals.

Locking system with 5-pin cylinder locks and modular barrels. Compatible with integrated locking systems.

Recessed open housing for ergonomic posture.

Fitted with:

Drawer front height (right) mm: 75, 100, 150, 200

Optional extras:

Additional accessories such as manual height adjustment, wheels, side panels, etc. can be found under GridLine individual components in Group 92.

Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts and cupboard doors RAL 7016 anthracite, **powder-coated**. **Drawer body not configurable, always RAL 7035 light grey.**

Technical description

Data sheet

Workbench/desk load capacity - maximum distributed load (on wood)	800 kg
Drawer usable width in G	20
Weight	132.6 kg
Drawer usable area in G	20×20
Drawer usable width	500 mm
Support cabinet width	1300 mm
Drawer usable depth	500 mm
Height	850 mm
Worktop depth	750 mm
Drawer body usable height	525 mm
Worktop length	1500 mm
Support cabinet depth	700 mm
Drawer usable depth in G	20
Series	Ready-to-go
Worktop thickness	50 mm
Number of drawers	4
Design version	Steel hollow section construction
Material thickness	1 mm
Workbench height	850 mm
Drawer/pull-out shelf load capacity	75 kg
Insert thickness	50 mm
Drawer runner extension (partial/full extension)	100 %
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20×20G
Type of product	Workbench

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/921004-1500>
