

Garant GRIDLINE

Workbench, left side cupboard, right side 4 drawers, Bamboo worktop, 20×20G, Worktop length: 1500 mm



Order data

Order number	921041 1500
GTIN	4062406086329
Item class	9GG

Description

NOTE: Colour selection possible

Version:

Workbench in sturdy steel construction with frame of rectangular hollow section. Drawer cabinet can be locked centrally with cylinder lock. **100% full extension drawers** with differential runners and 75 kg load capacity. Feet with plastic pads, do not damage the floor.

Drawer bodies always RAL 7035 light grey, **powder coated**. Variable colours for the drawer fronts. No surrounding ledges, thereby allowing optimum cleaning and full availability of the area for drawer dividers (boxes, rigid foam inlays, slotted partitions). Drawer runner mountings at 25 mm intervals.

Locking system with 5-pin cylinder locks and modular barrels. Compatible with integrated locking systems.

Body with cupboard and one inserted shelf.

Fitted with:

Door height (left) mm: 525

Number of height-adjustable shelves (left): 1

Drawer front height (right) mm: 75, 100, 150, 200

Optional extras:

Additional accessories such as manual height adjustment, wheels, side panels, etc. can be found under GridLine individual components in Group 92.

Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts and cupboard doors RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Workbench/desk load capacity - maximum distributed load (on wood): 800 kg

Drawer usable area in G: 20×20
 Height: 850 mm
 Worktop length: 1500 mm
 Worktop depth: 750 mm
 Worktop thickness: 50 mm
 Support cabinet width: 1300 mm
 Support cabinet depth: 700 mm

Technical description

Drawer usable depth in G	20
Worktop length	1500 mm
Drawer usable width in G	20
Drawer body usable height	525 mm
Support cabinet width	1300 mm
Weight	135.3 kg
Workbench/desk load capacity - maximum distributed load (on wood)	800 kg
Support cabinet depth	700 mm
Drawer usable width	500 mm
Drawer usable depth	500 mm
Worktop thickness	50 mm
Height	850 mm
Drawer usable area in G	20×20
Series	Ready-to-go
Worktop depth	750 mm
Number of drawers	4
Design version	Steel hollow section construction
Material thickness	1 mm
Workbench height	850 mm
Drawer/pull-out shelf load capacity	75 kg
Insert thickness	50 mm
Drawer runner extension (partial/full extension)	100 %

Door opening angle	180 degrees
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20x20G
Type of product	Complete workbench

Accessories

easyPick small parts storage bins set Drawer front height / type 75/1	950300 75/1
Marking out and sawing Number of tools 8	954895 8
Mat for drawers Dimension in G 20X20	951830 20X20
Drawer Drawer front height 200 mm	927800 200
Lock barrel with 2 keys Lock number Ho (3-digit) 003	950050 003
Slotted dividers / plain dividers set Drawer front height / type 75/1	950320 75/1
Hammer set Number of tools 3	954690 3
Slotted dividers / plain dividers set Drawer front height / type 100/2	950320 100/2
Pliers set Number of tools 5	954295 5
Comfort Close drawer closure damping system Load capacity of the drawer 75 kg	950180 75
Socket set 1/4 inch and 1/2 inch Number of tools 39	953833 39
Slotted dividers / plain dividers set Drawer front height / type 100/1	950320 100/1
Slotted dividers / plain dividers set Drawer front height / type 150/4	950320 150/4
Slotted dividers / plain dividers set Drawer front height / type 100/3	950320 100/3
easyPick small parts storage bins set Drawer front height / type 75/2	950300 75/2

Combination spanner set Number of tools 20	952505 20
File set Number of tools 6	952253 6
Socket set 1/4 inch and 1/2 inch Number of tools 37	953828 37
Drawer Drawer front height 100 mm	927800 100
Socket set 1/2 inch Number of tools 32	953821 32
Overlay of plasticised PVC transparent Width 1500 mm	951951 1500
Disassembly tool Type 1	950070 1
Drawer Drawer front height 150 mm	927800 150
Slotted dividers / plain dividers set Drawer front height / type 75/3	950320 75/3
Workshop set Number of tools 22	955071 22
Drawer Drawer front height 75 mm	927800 75
Slide handle for GridLine Type KO12	914226 KO12
Workshop set Number of tools 26	955081 26
Slotted dividers / plain dividers set Drawer front height / type 75/2	950320 75/2
Pliers set Number of tools 5	954305 5
Screwdriver set Number of tools 10	953521 10
Ribbed rubber mat for drawers Dimension in G 20X20	951910 20X20
Slotted dividers / plain dividers set Drawer front height / type 150/5	950320 150/5
easyPick small parts storage bins set Drawer front height / type 75/3	950300 75/3
Non-slip mats set for drawers, 5 pieces Dimension in G 20X20	951885 20X20
Cleaner and care oil set Type 1	926403 1
Lock plate for GridLine Type KO21	914227 KO21