

Garant GRIDLINE

Workbench, left side cupboard, right side 4 drawers, Beech marine ply worktop, 20×20G, Worktop length: 1500mm**Order data**

Order number	921044 1500
GTIN	4062406086336
Item class	9GG

Description**Version:**

Workbench in sturdy steel construction with frame of rectangular hollow section. Drawer cabinet can be locked centrally with cylinder lock. **100% full extension drawers** with differential runners and 75 kg load capacity. Feet with plastic pads, do not damage the floor.

Drawer bodies always RAL 7035 light grey, **powder coated**. Variable colours for the drawer fronts. No surrounding ledges, thereby allowing optimum cleaning and full availability of the area for drawer dividers (boxes, rigid foam inlays, slotted partitions). Drawer runner mountings at 25 mm intervals.

Locking system with 5-pin cylinder locks and modular barrels. Compatible with integrated locking systems.

Body with cupboard and one inserted shelf.

Fitted with:

Door height (left) mm: 525

Number of height-adjustable shelves (left): 1

Drawer front height (right) mm: 75, 100, 150, 200

Optional extras:

Additional accessories such as manual height adjustment, wheels, side panels, etc. can be found under GridLine individual components in Group 92.

Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts and cupboard doors RAL 7016 anthracite, **powder-coated**. **Drawer body not configurable, always RAL 7035 light grey.**

Technical description

Worktop depth	750 mm
Drawer body usable height	525 mm
Number of drawers	4
Drawer usable depth	500 mm
Support cabinet width	1300 mm
Drawer usable width in G	20
Drawer usable width	500 mm
Worktop length	1500 mm
Workbench/desk load capacity - maximum distributed load (on wood)	800 kg
Worktop thickness	50 mm
Height	850 mm
Series	Ready-to-go
Drawer usable depth in G	20
Support cabinet depth	700 mm
Drawer usable area in G	20×20
Weight	142.3 kg
Design version	Steel hollow section construction
Material thickness	1 mm
Workbench height	850 mm
Drawer/pull-out shelf load capacity	75 kg
Insert thickness	50 mm
Drawer runner extension (partial/full extension)	100 %
Door opening angle	180 degrees
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20×20G
Type of product	Workbench

Accessories

Slide handle for GridLine Type KO12	914226 KO12
Lock plate for GridLine Type KO21	914227 KO21
Drawer Drawer front height 100 mm	927800 100
Drawer Drawer front height 150 mm	927800 150
Drawer Drawer front height 200 mm	927800 200
Drawer Drawer front height 75 mm	927800 75
Lock barrel with 2 keys Lock number Ho (3-digit) 003	950050 003
Disassembly tool Type 1	950070 1
Comfort Close drawer closure damping system Load capacity of the drawer 75 kg	950180 75
easyPick small parts storage bin set Drawer front height / type 75/1	950300 75/1
easyPick small parts storage bin set Drawer front height / type 75/2	950300 75/2
easyPick small parts storage bin set Drawer front height / type 75/3	950300 75/3
Slotted dividers / plain dividers set Drawer front height / type 100/1	950320 100/1
Slotted dividers / plain dividers set Drawer front height / type 100/2	950320 100/2
Slotted dividers / plain dividers set Drawer front height / type 100/3	950320 100/3
Slotted dividers / plain dividers set Drawer front height / type 150/4	950320 150/4
Slotted dividers / plain dividers set Drawer front height / type 150/5	950320 150/5
Slotted dividers / plain dividers set Drawer front height / type 75/1	950320 75/1
	950320 75/2

Slotted dividers / plain dividers set Drawer front height / type 75/2	
Slotted dividers / plain dividers set Drawer front height / type 75/3	950320 75/3
Mat for drawers Dimension in G 20X20	951830 20X20
Non-slip mats set for drawers,5 pieces Dimension in G 20X20	951885 20X20
Ribbed rubber mat for drawers Dimension in G 20X20	951910 20X20
Overlay of plasticised PVC transparent Width 1500 mm	951951 1500
File set Number of tools 6	952253 6
Combination spanner set Number of tools 20	952505 20
Screwdriver set Number of tools 10	953522 10
Socket set 1/2 inch Number of tools 32	953821 32
Socket set 1/4 inch and 1/2 inch Number of tools 37	953828 37
Socket set 1/4 inch and 1/2 inch Number of tools 39	953833 39
Pliers set Number of tools 5	954295 5
Pliers set Number of tools 5	954305 5
Pliers set Number of tools 5	954306 5
Marking out and sawing Number of tools 8	954895 8
Workshop set Number of tools 22	955071 22
Workshop set Number of tools 22	955072 22
Workshop set Number of tools 26	955081 26