

Garant GRIDLINE

Workbench, left side 5 drawers, centre open, right side 4 drawers, Bamboo worktop, 20×20G, Worktop length: 2000mm**Order data**

Order number	921201 2000
GTIN	4062406086411
Item class	9GG

Description**Version:**

Workbench in sturdy steel construction with frame of rectangular hollow section. Drawer cabinet can be locked centrally with cylinder lock. **100% full extension drawers** with differential runners and 75 kg load capacity. Feet with plastic pads, do not damage the floor.

Centre part with recessed open housing for ergonomic posture.

Drawer bodies always RAL 7035 light grey, **powder coated**. Variable colours for the drawer fronts. No surrounding ledges, thereby allowing optimum cleaning and full availability of the area for drawer dividers (boxes, rigid foam inlays, slotted partitions). Drawer runner mountings at 25 mm intervals.

Locking system with 5-pin cylinder locks and modular barrels. Compatible with integrated locking systems.

Fitted with:

Drawer front height (left) mm: 75, 75, 125, 125, 125

Drawer front height (right) mm: 75, 100, 150, 200

Optional extras:

Additional accessories such as manual height adjustment, wheels, side panels, etc. can be found under GridLine individual components in Group 92.

Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts and cupboard doors RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Technical description

Number of drawers	9
Series	Ready-to-go
Weight	202.4 kg
Height	850 mm
Worktop depth	750 mm
Support cabinet depth	700 mm
Worktop length	2000 mm
Drawer usable area in G	20×20
Workbench/desk load capacity - maximum distributed load (on wood)	800 kg
Drawer usable width in G	20
Drawer body usable height	525 mm
Drawer usable width	500 mm
Worktop thickness	50 mm
Support cabinet width	1900 mm
Drawer usable depth	500 mm
Drawer usable depth in G	20
Design version	Steel hollow section construction
Material thickness	1 mm
Workbench height	850 mm
Drawer/pull-out shelf load capacity	75 kg
Insert thickness	50 mm
Drawer runner extension (partial/full extension)	100 %
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20×20G
Type of product	Workbench

Accessories

Drawer Drawer front height 200 mm	927800 200
Drawer Drawer front height 150 mm	927800 150
Lock plate for GridLine Type KO21	914227 KO21
Lock barrel with 2 keys Lock number Ho (3-digit) 003	950050 003
Cleaner and care oil set Type 1	926403 1
Drawer Drawer front height 100 mm	927800 100
Drawer Drawer front height 75 mm	927800 75