

Garant GRIDLINE

## Workbench, left side cupboard, centre open, right side 4 drawers, Bamboo worktop, 20×20G, Worktop length: 2000 mm



### Order data

Order number	921161 2000
GTIN	4062406086350
Item class	9GG

### Description

#### NOTE: Colour selection possible

#### Version:

Workbench in sturdy steel construction with frame of rectangular hollow section. Drawer cabinet can be locked centrally with cylinder lock. **100% full extension drawers** with differential runners and 75 kg load capacity. Feet with plastic pads, do not damage the floor.

Centre part with recessed open casing for ergonomic posture. Body with door and height-adjustable shelf.

Drawer bodies always RAL 7035 light grey, **powder coated**. Variable colours for the drawer fronts. No surrounding ledges, thereby allowing optimum cleaning and full availability of the area for drawer dividers (boxes, rigid foam inlays, slotted partitions). Drawer runner mountings at 25 mm intervals.

Locking system with 5-pin cylinder locks and modular barrels. Compatible with integrated locking systems.

#### Fitted with:

Door height (left) mm: 525

Number of height-adjustable shelves (left): 1

Drawer front height (right) mm: 75, 100, 150, 200

#### Optional extras:

Additional accessories such as manual height adjustment, wheels, side panels, etc. can be found under GridLine individual components in Group 92.

#### Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts and cupboard doors RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Workbench/desk load capacity - maximum distributed load (on wood): 800 kg

Drawer usable area in G: 20×20  
 Height: 850 mm  
 Worktop length: 2000 mm  
 Worktop depth: 750 mm  
 Worktop thickness: 50 mm  
 Support cabinet width: 1900 mm  
 Support cabinet depth: 700 mm

## Technical description

Worktop length	2000 mm
Number of drawers	4
Series	Ready-to-go
Drawer body usable height	525 mm
Worktop thickness	50 mm
Drawer usable depth in G	20
Drawer usable width in G	20
Worktop depth	750 mm
Drawer usable width	500 mm
Workbench/desk load capacity - maximum distributed load (on wood)	800 kg
Drawer usable depth	500 mm
Weight	165.3 kg
Height	850 mm
Drawer usable area in G	20×20
Support cabinet depth	700 mm
Support cabinet width	1900 mm
Design version	Steel hollow section construction
Material thickness	1 mm
Workbench height	850 mm
Drawer/pull-out shelf load capacity	75 kg
Insert thickness	50 mm
Drawer runner extension (partial/full extension)	100 %

Door opening angle	180 degrees
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20x20G
Type of product	Complete workbench

## Accessories

Comfort Close drawer closure damping system Load capacity of the drawer 75 kg	950180 75
Slotted dividers / plain dividers set Drawer front height / type 100/1	950320 100/1
Pliers set Number of tools 5	954305 5
Slotted dividers / plain dividers set Drawer front height / type 75/3	950320 75/3
Drawer Drawer front height 100 mm	927800 100
Drawer Drawer front height 200 mm	927800 200
Drawer Drawer front height 150 mm	927800 150
File set Number of tools 6	952253 6
Screwdriver set Number of tools 10	953521 10
Slotted dividers / plain dividers set Drawer front height / type 150/4	950320 150/4
Lock plate for GridLine Type KO21	914227 KO21
Marking out and sawing Number of tools 8	954895 8
Overlay of plasticised PVC transparent Width 2000 mm	951951 2000
easyPick small parts storage bins set Drawer front height / type 75/1	950300 75/1
Drawer Drawer front height 75 mm	927800 75
Slotted dividers / plain dividers set Drawer front height / type 100/2	950320 100/2

Combination spanner set Number of tools 20	952505 20
Non-slip mats set for drawers, 5 pieces Dimension in G 20X20	951885 20X20
Socket set 1/4 inch and 1/2 inch Number of tools 39	953833 39
Slotted dividers / plain dividers set Drawer front height / type 75/2	950320 75/2
Hammer set Number of tools 3	954690 3
easyPick small parts storage bins set Drawer front height / type 75/3	950300 75/3
Lock barrel with 2 keys Lock number Ho (3-digit) 003	950050 003
Socket set 1/4 inch and 1/2 inch Number of tools 37	953828 37
Workshop set Number of tools 22	955071 22
Slotted dividers / plain dividers set Drawer front height / type 100/3	950320 100/3
Slide handle for GridLine Type KO12	914226 KO12
Disassembly tool Type 1	950070 1
Workshop set Number of tools 26	955081 26
Slotted dividers / plain dividers set Drawer front height / type 75/1	950320 75/1
easyPick small parts storage bins set Drawer front height / type 75/2	950300 75/2
Socket set 1/2 inch Number of tools 32	953821 32
Ribbed rubber mat for drawers Dimension in G 20X20	951910 20X20
Cleaner and care oil set Type 1	926403 1
Slotted dividers / plain dividers set Drawer front height / type 150/5	950320 150/5
Pliers set Number of tools 5	954295 5
Mat for drawers Dimension in G 20X20	951830 20X20