

Garant GRIDLINE

Workbench, left side cupboard, centre open, right side 4 drawers, Beech marine ply worktop, 20×20G, Worktop length: 2000mm**Order data**

Order number	921174 2000
GTIN	4062406086398
Item class	9GG

Description**Version:**

Workbench in sturdy steel construction with frame of rectangular hollow section. Drawer cabinet can be locked centrally with cylinder lock. **100% full extension drawers** with differential runners and 75 kg load capacity. Feet with plastic pads, do not damage the floor.

Drawer bodies always RAL 7035 light grey, **powder coated**. Variable colours for the drawer fronts. No surrounding ledges, thereby allowing optimum cleaning and full availability of the area for drawer dividers (boxes, rigid foam inlays, slotted partitions). Drawer runner mountings at 25 mm intervals.

Locking system with 5-pin cylinder locks and modular barrels. Compatible with integrated locking systems.

Centre part with recessed open casing for ergonomic posture. Body with door and height-adjustable shelf.

Fitted with:

Door height (left) mm: 625

Number of height-adjustable shelves (left): 1

Drawer front height (right) mm: 100, 125, 150, 250

Optional extras:

Additional accessories such as manual height adjustment, wheels, side panels, etc. can be found under GridLine individual components in Group 92.

Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts and cupboard doors RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Technical description

Series	Ready-to-go
Drawer usable width in G	20
Workbench/desk load capacity - maximum distributed load (on wood)	800 kg
Drawer body usable height	625 mm
Number of drawers	4
Worktop length	2000 mm
Drawer usable depth in G	20
Worktop depth	750 mm
Drawer usable depth	500 mm
Worktop thickness	50 mm
Support cabinet depth	700 mm
Support cabinet width	1900 mm
Drawer usable area in G	20×20
Drawer usable width	500 mm
Height	950 mm
Weight	184.2 kg
Design version	Steel hollow section construction
Material thickness	1 mm
Workbench height	950 mm
Drawer/pull-out shelf load capacity	75 kg
Insert thickness	50 mm
Drawer runner extension (partial/full extension)	100 %
Door opening angle	180 degrees
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20×20G
Type of product	Workbench

Accessories

Lock barrel with 2 keys Lock number Ho (3-digit) 003	950050 003
Lock plate for GridLine Type KO21	914227 KO21
Drawer Drawer front height 125 mm	927800 125
Slide handle for GridLine Type KO12	914226 KO12
Drawer Drawer front height 100 mm	927800 100
Drawer Drawer front height 250 mm	927800 250
Drawer Drawer front height 150 mm	927800 150