

Garant GRIDLINE

Workbench with electric height adjustment, left side 5 drawers, centre open, right side 4 drawers, Beech marine ply worktop, 20×20G, Worktop length: 2000/DE mm



Order data

Order number	921604 2000/DE
GTIN	4062406086572
Item class	9GG

Description

Version:

Workbench in sturdy steel construction with frame of rectangular hollow section. Drawer cabinet can be locked centrally with cylinder lock. **100% full extension drawers** with differential runners and 75 kg load capacity.

Stepless electric drive for height adjustment. Height adjustment by pushbutton. Connecting cable with German Schuko plug. Power supply 250 V / 50 Hz with maximum 340 W. Length of the connecting cable 1.5 m.

Centre part with recessed open housing for ergonomic posture.

Drawer bodies always RAL 7035 light grey, **powder coated**. Variable colours for the drawer fronts. No surrounding ledges, thereby allowing optimum cleaning and full availability of the area for drawer dividers (boxes, rigid foam inlays, slotted partitions). Drawer runner mountings at 25 mm intervals.

Locking system with 5-pin cylinder locks and modular barrels. Compatible with integrated locking systems.

Function:

IP20: Protected against penetration by foreign bodies with $\varnothing < 12$ mm, however touching should be avoided, and offers no protection against water.

Fitted with:

Drawer front height (left) mm: 75, 75, 125, 125, 125

Drawer front height (right) mm: 75, 100, 150, 200

Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts and cupboard doors RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Note:

When benches are installed in a row, it is essential that additional side plates No. 927220 are fitted.

Drawer usable area in G: 20×20

IP Index of Protection: IP 20

Height adjustment range: 850 - 1050 mm

Worktop length: 2000 mm

Worktop depth: 750 mm

Worktop thickness: 50 mm

Support cabinet width: 1900 mm

Support cabinet depth: 700 mm

Technical description

Worktop length	2000 mm
Principle of height adjustment	electrical
Weight	230.2 kg
Supply voltage	250 V
Drawer usable area in G	20×20
Series	Ready-to-go
Support cabinet depth	700 mm
Drawer usable depth in G	20
Drawer usable width	500 mm
Drawer usable depth	500 mm
Number of drawers	9
maximum lifting force	6000 N
Worktop depth	750 mm
Stepless height adjustment	yes
Worktop thickness	50 mm
Lifting speed	9 mm/s
Drawer body usable height	525 mm
Support cabinet width	1900 mm
ComfortClose	no
Drawer usable width in G	20

Electronic locking system can be retrofitted	yes
Height adjustment range	850 - 1050 mm
IP Index of Protection	IP 20
Power supply	Rechargeable battery-powered
Power supply	Mains operated
Design version	Steel hollow section construction
Material thickness	1 mm
Height adjustment workstation	850-1050 mm
Drawer/pull-out shelf load capacity	75 kg
Workbench/desk load capacity - maximum distributed load (on wood)	350 kg
Type of height adjustment	electrical
Insert thickness	50 mm
Drawer runner extension (partial/full extension)	100 %
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20x20G
Type of product	Workbench with electric height adjustment

Accessories

Overlay of plasticised PVC transparent Width 2000 mm	951951 2000
File set Number of tools 6	952253 6
Combination spanner set Number of tools 20	952505 20
Screwdriver set Number of tools 10	953521 10
Socket set 1/2 inch Number of tools 32	953821 32
Socket set 1/4 inch and 1/2 inch Number of tools 37	953828 37
Socket set 1/4 inch and 1/2 inch Number of tools 39	953833 39

Pliers set Number of tools 5	954295 5
Pliers set Number of tools 5	954305 5
Hammer set Number of tools 3	954690 3
Marking out and sawing Number of tools 8	954895 8
Lock plate for GridLine Type KO21	914227 KO21
Drawer Drawer front height 100 mm	927800 100
Drawer Drawer front height 150 mm	927800 150
Drawer Drawer front height 200 mm	927800 200
Drawer Drawer front height 75 mm	927800 75
Mat for drawers Dimension in G 20X20	951830 20X20
Non-slip mats set for drawers, 5 pieces Dimension in G 20X20	951885 20X20
Ribbed rubber mat for drawers Dimension in G 20X20	951910 20X20
easyPick small parts storage bins set Drawer front height / type 75/1	950300 75/1
easyPick small parts storage bins set Drawer front height / type 75/2	950300 75/2
easyPick small parts storage bins set Drawer front height / type 75/3	950300 75/3
Slotted dividers / plain dividers set Drawer front height / type 100/1	950320 100/1
Slotted dividers / plain dividers set Drawer front height / type 100/2	950320 100/2
Slotted dividers / plain dividers set Drawer front height / type 100/3	950320 100/3
Slotted dividers / plain dividers set Drawer front height / type 75/1	950320 75/1
Slotted dividers / plain dividers set Drawer front height / type 75/2	950320 75/2
Slotted dividers / plain dividers set Drawer front height / type 75/3	950320 75/3
Slotted dividers / plain dividers set Drawer front height / type 125/1	950320 125/1

Slotted dividers / plain dividers set Drawer front height / type 125/2	950320 125/2
Slotted dividers / plain dividers set Drawer front height / type 125/3	950320 125/3
Slotted dividers / plain dividers set Drawer front height / type 125/4	950320 125/4
Slotted dividers / plain dividers set Drawer front height / type 125/6	950320 125/6
Slotted dividers / plain dividers set Drawer front height / type 150/4	950320 150/4
Slotted dividers / plain dividers set Drawer front height / type 150/5	950320 150/5
Comfort Close drawer closure damping system Load capacity of the drawer 75 kg	950180 75
Workshop set Number of tools 22	955071 22
Workshop set Number of tools 26	955081 26
Lock barrel with 2 keys Lock number Ho (3-digit) 003	950050 003
Disassembly tool Type 1	950070 1