

Garant GRIDLINE

**Vario Basic workbench, height 850 mm, Beech marine ply worktop, Worktop length: 1500mm****Order data**

Order number	922004 1500
GTIN	4062406086657
Item class	9GG

**Description****Version:**

Workbench in sturdy steel construction. Support legs 50 mm wide with cross bracing and mounting for height adjustment. Feet with plastic pads, do not damage the floor. With 2 pairs of stabilising plates for stiffening.

**Supplied with:**

2 × support legs, 2 × pairs of stabilising plates, worktop.

**Optional extras:**

Additional accessories such as manual height adjustment, wheels, side panels, etc. can be found under GridLine individual components in Group 92.

**Colour:**

Body and supports light grey RAL 7035, **powder-coated**.

**Note:**

Supplied for self-assembly, saving freight costs. Delivered unassembled.

**Technical description**

Height	850 mm
Worktop thickness	50 mm
Worktop depth	750 mm
Weight	59 kg

Series	vario Basic
Worktop length	1500 mm
Design version	Steel hollow section construction
Material thickness	1 mm
Workbench height	850 mm
Workbench/desk load capacity - maximum distributed load (on wood)	400 kg
Insert thickness	50 mm
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Work table

---

## Accessories

Worktop thickness 50 mm of beech marine ply Worktop length 1500 mm	926081 1500
Stabilising plate Type 1	927122 1
Support leg Height 800 mm	927000 800