

Garant GRIDLINE

Vario Basic workbench, height 950 mm, Beech marine ply worktop, Worktop length: 1500mm**Order data**

Order number	922014 1500
GTIN	4062406086848
Item class	9GG

Description**Version:**

Workbench in sturdy steel construction. Support legs 50 mm wide with cross bracing and mounting for height adjustment. Feet with plastic pads, do not damage the floor. With 2 pairs of stabilising plates for stiffening.

Supplied with:

2 × support legs, 2 × pairs of stabilising plates, worktop.

Optional extras:

Additional accessories such as manual height adjustment, wheels, side panels, etc. can be found under GridLine individual components in Group 92.

Colour:

Body and supports light grey RAL 7035, **powder-coated.**

Note:

Supplied for self-assembly, saving freight costs. Delivered unassembled.

Technical description

Height	950 mm
Worktop thickness	50 mm
Worktop length	1500 mm
Weight	61 kg

Series	vario Basic
Design version	Steel hollow section construction
Material thickness	1 mm
Workbench height	950 mm
Workbench/desk load capacity - maximum distributed load (on wood)	400 kg
Insert thickness	50 mm
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Work table

Accessories

Stabilising plate Type 1	927122 1
Worktop thickness 50 mm of beech marine ply Worktop length 1500 mm	926081 1500
Support leg Height 900 mm	927000 900