

Garant GRIDLINE

Vario Basic workbench, height 950 mm, Eluplan worktop, dark, Worktop length: 1000mm**Order data**

Order number	922017 1000
GTIN	4062406086862
Item class	9GG

Description**Version:**

Workbench in sturdy steel construction. Support legs 50 mm wide with cross bracing and mounting for height adjustment. Feet with plastic pads, do not damage the floor. With 2 pairs of stabilising plates for stiffening.

Supplied with:

2 × support legs, 2 × pairs of stabilising plates, worktop.

Optional extras:

Additional accessories such as manual height adjustment, wheels, side panels, etc. can be found under GridLine individual components in Group 92.

Colour:

Body and supports light grey RAL 7035, **powder-coated.**

Note:

Supplied for self-assembly, saving freight costs. Delivered unassembled.

Technical description

Height	950 mm
Material of worktop	Eluplan

Worktop depth	750 mm
Worktop length	1000 mm
Series	vario Basic
Worktop thickness	50 mm
Weight	46 kg
Design version	Steel hollow section construction
Material thickness	1 mm
Workbench height	950 mm
Workbench/desk load capacity - maximum distributed load (on wood)	400 kg
Insert thickness	50 mm
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Work table

Accessories

Stabilising plate Type 1	927122 1
Worktop with dark grey plastic coating (Eluplan) Worktop length 1000 mm	926241 1000
Support leg Height 900 mm	927000 900