

Garant GRIDLINE

Vario Basic workbench, height 950 mm, Bamboo worktop, Worktop length: 1500mm**Order data**

| | |
|--------------|---------------|
| Order number | 922011 1500 |
| GTIN | 4062406086817 |
| Item class | 9GG |

Description**Version:**

Workbench in sturdy steel construction. Support legs 50 mm wide with cross bracing and mounting for height adjustment. Feet with plastic pads, do not damage the floor. With 2 pairs of stabilising plates for stiffening.

Supplied with:

2 × support legs, 2 × pairs of stabilising plates, worktop.

Optional extras:

Additional accessories such as manual height adjustment, wheels, side panels, etc. can be found under GridLine individual components in Group 92.

Colour:

Body and supports light grey RAL 7035, **powder-coated.**

Note:

Supplied for self-assembly, saving freight costs. Delivered unassembled.

Technical description

| | |
|---------------------|-------------|
| Worktop thickness | 50 mm |
| Material of worktop | Bamboo |
| Series | vario Basic |
| Weight | 61 kg |

| | |
|---|--|
| Worktop depth | 750 mm |
| Worktop length | 1500 mm |
| Height | 950 mm |
| Design version | Steel hollow section construction |
| Material thickness | 1 mm |
| Workbench height | 950 mm |
| Workbench/desk load capacity - maximum distributed load (on wood) | 400 kg |
| Insert thickness | 50 mm |
| Colour selection | RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003 |
| Type of product | Work table |

Accessories

| | |
|--|-------------|
| Support leg Height 900 mm | 927000 900 |
| Worktop thickness 50 mm of bamboo strips glued cross-wise Worktop length 1500 mm | 926001 1500 |
| Stabilising plate Type 1 | 927122 1 |