



## Workshop compressor, Type: I.COMP3



### Order data

Order number	079841 I.COMP3
GTIN	
Item class	03R

### Description

#### Version:

Corrosion-free valves, highly efficient cooling, maintenance-free transmission components, corrosion-protected reservoir, minimum 10-year spare parts availability guarantee. High efficiency for low operating costs. Portable and wheeled workman's compressor, oil-free and water-free.

- **oil-free compressed air.**
- **lightweight for transport.**
- **for general-purpose use.**
- **integral pressure selection and stepless speed variation.**

#### Note:

Other workshop compressors available on request.

### Technical description

Manufacturer's designation	i.Comp 3
maximum pressure (air)	11 bar
Width	570 mm

Pressure vessel volume	117 l
maximum filling rate	160 l/min
maximum suction rate	265 l/min
Power consumption	1.5 kW
Operating noise	97 dB(A)
Height	1050 mm
Length	440 mm
maximum speed	3200 min <sup>-1</sup>
Weight	29 kg
Type of product	Compressor