


**KOMET® arbor, SK 50, ABS® Ø d: 25 mm**

**Order data**

Order number	239002 25
GTIN	4047109045163
Item class	29W

**Description**
**Version:**

- Form AD/B
- Arbor balanced to Q 6.3 at 8000 rpm.
- With through coolant feed.

**Standard:**
**DIN 69871**
**Supplied with:**
**Complete with sealing washer and conversion set for form AD.**
**Note:**

Further arbors with ABS® connection on request.

Through-coolant: yes

Overhang A: 60 mm

 Projection length L<sub>1</sub>: 20 mm

**Technical description**

ABS® shank Ø D <sub>s</sub>	25 mm
Projection length L <sub>1</sub>	20 mm
Overhang A	60 mm
Adapter	SK 50
Shank	ABS
Arbor standard	DIN 69871

Shape	ADB
Balance quality G at rotational speed	G 6.3 at 8,000 rpm
Through-coolant	yes
Type of product	ABS mounting