



Neigungsmesstechnik o.K.

Square type spirit level, Base Length×Accuracy: 200/2mm



Order data

Order number	469210 200/2
GTIN	4030616426204
Item class	46U

Description

Version:

Sturdy frame of high quality special casting; hammer finish. 3 sides prismatic and flat. 1 side flat, all precision ground. One longitudinal and one transverse vial each of glass. The sensitivity (scale value) of the longitudinal vial is specified on the square.

Thermal insulation over the entire body protects against the effects of the heat of hands or breath. Recess in the body permits a side view of the vial.

Application:

For aligning horizontal and vertical faces, shafts etc. and for accurate alignment at a 90° angle.

Standard:

DIN 877

Accuracy:

1 = with very high sensitivity longitudinal vial **0.02 mm/m.**

2 = with high sensitivity longitudinal vial **0.1 mm/m.**

Note:

Magnetic version available on request.

Technical description

Sole length	200 mm
-------------	--------

Sole width	42 mm
Scale divisions	0.1 mm/m
Accuracy class	2
Standard	DIN 877
Packaging	sturdy box
Calibration	H1
Type of product	Spirit level

Services

Calibration Square frame level Accuracy 0,10 mm/m	026600 0,10
---	-------------