



## Screw jack with magnetic base, highest support height: 88Fmm



### Order data

Order number	373550 88F
GTIN	4020772072865
Item class	35A

### Description

#### Version:

Self-locking trapezoidal thread spindle with end stop.

The permanent magnet in the base of the screw jack ensures simple, lasting and precise positioning of the workpiece **on vertical faces**. Modular version. Height extension up to a maximum of 350 mm, in combination with the spacer ring No. 373555.

#### Note:

With centring hole  $\varnothing$  12 mm for jack pads No. 375000 - 375010.

### Technical description

highest support height	88 mm
Head $\varnothing$	50 mm
lowest support height	75 mm
Type	6400
Lower part $\varnothing$	50 mm
for clamp with slot width	14 - 22 mm

Load capacity	30 kN
Type of product	Screw jack