

**LED torch with batteries, Colour: BLACK****Order data**

Order number	081437 BLACK
GTIN	4062406087364
Item class	02A

Description**Version:**

High-quality, long-life and sturdy LED torch of anodised aluminium. **Latest LED technology** with **outstanding lighting power**.

- **Anti-roll protection.**
- **Rubber cover for the operating button.**

With **focussable** lamp head.

In various colours.

Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

IP Index of Protection: IP 54

Torch function: Focus

ATEX zone: no

Illumination: 250 lm

Illumination step 2: 100 lm

Working life: 4 h

Lighting life stage 2: 12 h

Number of batteries contained: 3

Technical description

Head Ø	27 mm
Including belt pocket	no
Illumination step 2	100 lm
IP Index of Protection	IP 54
Battery type	Micro, AAA
Working life	4 h
ATEX zone	no
Lighting life stage 2	12 h
Colour of housing	BLACK
Number of batteries contained	3
Illumination	250 lm
Bulb	LED module
Torch function	Focus
Overall length	143 mm
Power supply	Battery-powered
Type of product	Flashlight

Accessories

Alkaline-manganese batteries International size LR3	081552 LR3
Alkaline-manganese batteries International size LR3	081551 LR3
Alkaline manganese battery set International size LR3	081558 LR3
Alkaline manganese battery set International size LR3	081557 LR3
Alkaline-manganese batteries International size LR3	081561 LR3
Alkaline-manganese batteries International size LR3	081554 LR3
Battery holder Version 3AAA	081506 3AAA
Lithium-metal batteries International size LR3	081559 LR3

Alkaline-manganese batteries International size LR3

081553 LR3