

**LED torch with batteries, Colour: SILVER****Order data**

Order number	081437 SILVER
GTIN	4062406087388
Item class	02A

Description**Version:**

High-quality, long-life and sturdy LED torch of anodised aluminium. **Latest LED technology** with **outstanding lighting power**.

- **Anti-roll protection.**
- **Rubber cover for the operating button.**

With **focussable** lamp head.

In various colours.

Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

Technical description

Illumination step 2	100 lm
Battery type	Micro, AAA
ATEX zone	no
IP Index of Protection	IP 54

Illumination time	4 h
Head Ø	27 mm
Illumination	250 lm
Bulb	LED module
Colour of housing	SILVER
#Number of batteries contained	3
Illumination time stage 2	12 h
Torch function	Focus
Overall length	143 mm
Power supply	Battery-powered
Type of product	Flashlight

Accessories

Battery holder Version 3AAA	081506 3AAA
Alkaline-manganese batteries International size LR3	081551 LR3
Alkaline-manganese batteries International size LR3	081552 LR3
Alkaline-manganese batteries International size LR3	081553 LR3
Alkaline-manganese batteries International size LR3	081554 LR3
Lithium-metal batteries International size LR3	081559 LR3
Alkaline-manganese batteries International size LR3	081561 LR3