

Garant
Trapezoidal hand tap set, uncoated, Tr: TR8X1,5

Order data

Order number	130760 TR8X1,5
GTIN	4062406086947
Item class	11G

Description
Version:

3-piece set, **consisting of taper, second, and plug tap.**

- **Taper tap with long pilot pin**
- **Plug tap tolerance H7**

Note:

Tool unsuitable for reversing out.

Thread pitch: 1.5 mm

Overall length L: 80 mm

Shank $\varnothing D_s$: 6 mm

Shank square \square : 4.9 mm

Tapping hole \varnothing : 6.6 mm

Technical description

Overall length L	80 mm
Tapping hole \varnothing	6.6 mm
Number of cutting edges Z	3
Number of clamping slots	3
Shank $\varnothing D_s$	6 mm
Shank square \square	4.9 mm
Thread pitch	1.5 mm

Thread size	8
Coating	uncoated
Thread type	TR
Flank angle	30 degrees
Tool material	HSS E
Standard	Manufacturer's standard
Tolerance class	DIN 103 7H
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 1.5xD for through holes
Cutting direction	right-hand
Type of threading tool	Hand tap
Colour ring	without
Type of product	Tap