

Garant
Trapezoidal hand tap set, uncoated, Tr: TR14X3

Order data

Order number	130760 TR14X3
GTIN	4062406087517
Item class	11G

Description
Version:

3-piece set, **consisting of taper, second, and plug tap.**

- **Taper tap with long pilot pin**
- **Plug tap tolerance H7**

Note:

Tool unsuitable for reversing out.

Thread pitch: 3 mm

Overall length L: 130 mm

Shank $\varnothing D_s$: 10 mm

Shank square \square : 8 mm

Tapping hole \varnothing : 11.25 mm

Technical description

Shank square \square	8 mm
Shank $\varnothing D_s$	10 mm
Number of cutting edges Z	3
Tapping hole \varnothing	11.25 mm
Thread pitch	3 mm
Overall length L	130 mm
Number of clamping slots	3

Thread size	14
Coating	uncoated
Thread type	TR
Flank angle	30 degrees
Tool material	HSS E
Standard	Manufacturer's standard
Tolerance class	DIN 103 7H
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 1.5xD for through holes
Cutting direction	right-hand
Type of threading tool	Hand tap
Colour ring	without
Type of product	Tap