

**Garant**
**Individual trapezoidal hand tap Plug tap, uncoated, Tr: TR10X2**

**Order data**

Order number	130790 TR10X2
GTIN	4062406087784
Item class	11G

**Description**
**Version:**

3-piece set, **consisting of taper, second, and plug tap.**

- **Taper tap with long pilot pin**
- **Plug tap tolerance H7**

**Note:**

**Tool unsuitable for reversing out.**

Thread pitch: 2 mm

Overall length L: 90 mm

Shank  $\varnothing D_s$ : 7 mm

Shank square  $\square$ : 5.5 mm

Tapping hole  $\varnothing$ : 8.2 mm

**Technical description**

Shank square $\square$	5.5 mm
Thread pitch	2 mm
Tapping hole $\varnothing$	8.2 mm
Number of cutting edges Z	3
Shank $\varnothing D_s$	7 mm
Number of clamping slots	3
Overall length L	90 mm
Thread size	10
Coating	uncoated

Thread type	TR
Flank angle	30 degrees
Tool material	HSS E
Standard	Manufacturer's standard
Tolerance class	DIN 103 7H
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 1.5×D for through holes
Cutting direction	right-hand
Type of threading tool	Hand tap
Colour ring	without
Type of product	Tap