



## COLOUR MATCH LED true colour work lamps, Type: MINI



### Order data

Order number	081513 MINI
GTIN	5708997356500
Item class	08C

### Description

#### Version:

**COLOUR MATCH.** Special LED with high CRI value for **perfect colour reproduction** and extremely long LED working life. Perfect for all painting, polishing, cleaning and preparation work. Designed for use in paint shops. **Exchangeable glass lens** and resistant to all types of solvent, even when cleaned every day. **MINIMATCH.** With a 2 COLOUR LIGHT function. This allows the choice between two colour temperatures depending on the work in hand. Warm light (4500 K) for light surfaces and cold light (6500 K) for dark surfaces.

Rechargeable dust-proof and waterproof cordless hand-held work lamp. With sturdy swivel hook and powerful built-in magnet. Flexible lamp head (swings through 180°).

#### Function:

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

#### Supplied with:

Charging cable.

### Technical description

Type of rechargeable battery	Lithium-ion
Light colour	cold white

Light colour	true colour
Light colour	warm white
Illumination	200 lm
Battery voltage	3.7 V
Battery capacity	1.6 Ah
Power supply	Rechargeable battery powered
Number of rechargeable batteries contained	1
Colour temperature	4500 - 6500 K
CRI value	96
IP Index of Protection	IP 65
Overall width	60 mm
Illumination time	2 h
Overall length	156 mm
Weight	190 g
ATEX zone	no
Type of product	Work lamp