

SWISS TOOLS

Cutting head, left-hand, Shank Ø / insert size: 40/12 mm



Order data

Order number	260013 40/12
GTIN	2050001912220
Item class	29D

Description

Version:

Interchangeable cutting heads for HSK-T and PSC base bodies. Optimum cooling via aligned High Pressure Cooling nozzles.

Suitable for :

Boring bar base body **No. 320102; 320103; 320407; 320408.**

Through-coolant: yes

Cutting point / joint: 40 mm

ISO code indexable cutting head: SCLCR/L

suitable indexable insert: CC.. 1204..

Minimum pre-drill Ø D_{min} : 50 mm

Centre-line offset: 27 mm

Overall length: 40 mm

Technical description

ISO code indexable cutting head	SCLCR/L
Minimum pre-drill Ø D_{min}	50 mm
Cutting point / joint	40 mm

suitable indexable insert	CC.. 1204..
Centre-line offset	27 mm
Insert size	12 mm
Spare parts	320620_2
Shank Ø	40 mm
Overall length	40 mm
Insert assignment	right-hand and neutral
Series	Cutting head
Application type	left-hand
Through-coolant	yes

Accessories

Torx-screw No. 2 Type 2	320620 2
-------------------------	----------