



LED true colour rechargeable work lamp, Type: MULTI3



Order data

Order number	081514 MULTI3
GTIN	5708997356531
Item class	08C

Description

Version:

COLOUR MATCH. Special LED with high CRI value for **perfect colour reproduction** and extremely long LED working life. Perfect for all painting, polishing, cleaning and preparation work. Designed for use in paint shops. **Exchangeable glass lens** and resistant to all types of solvent, even when cleaned every day. **MULTIMATCH 3.** Powerful portable cordless work light with selector switch for 5 colour temperatures. Display at the back, showing the battery capacity and remaining working time. Integral adjustment base for direct mounting on Scangrip stand 081252 1.35-3.

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

Including battery charger.

IP Index of Protection: IP 67

ATEX zone: no

Illumination: 3000 lm

Working life: 15 h

CRI value: 96

Number of rechargeable batteries contained: 1

Type of rechargeable battery: Lithium-ion

Technical description

Light colour	true colour
Illumination	3000 lm
Working life	15 h
Battery capacity	4 A·h
Number of rechargeable batteries contained	1
Battery voltage	11.1 V
ATEX zone	no
IP Index of Protection	IP 67
Power supply	Rechargeable battery-powered
Type of rechargeable battery	Lithium-ion
Overall length	240 mm
Overall width	230 mm
CRI value	96
Weight	1970 g
Manufacturer's designation	MULTIMATCH 3
Type of product	Work lamp