



COLOUR MATCH LED true colour work lamps, Type: SUN3



Order data

Order number	081513 SUN3
GTIN	5708997356517
Item class	08C

Description

Version:

COLOUR MATCH. Special LED with high CRI value for **perfect colour reproduction** and extremely long LED working life. Perfect for all painting, polishing, cleaning and preparation work. Designed for use in paint shops. **Exchangeable glass lens** and resistant to all types of solvent, even when cleaned every day. **SUNMATCH 3.** Cordless LED hand-held work lamp with selector switch for 5 colour temperatures (ALL DAYLIGHT function).

Rechargeable dust-proof and waterproof cordless hand-held work lamp. With sturdy swivel hook and powerful built-in magnet. Flexible lamp head (swings through 180°).

Function:

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

Supplied with charger and USB cable.

IP Index of Protection: IP 65

ATEX zone: no

Illumination: 500 lm

Working life: 4 h

CRI value: 96

Number of rechargeable batteries contained: 1

Type of rechargeable battery: Lithium-ion

Technical description

Number of rechargeable batteries contained	1
Type of rechargeable battery	Lithium-ion
Battery capacity	2.6 A·h
Illumination	500 lm
Battery voltage	3.7 V
Light colour	true colour
Power supply	Rechargeable battery powered
Working life	4 h
Overall width	60 mm
IP Index of Protection	IP 65
CRI value	96
Overall length	190 mm
Weight	270 g
ATEX zone	no
Manufacturer's designation	SUNMATCH 3
Type of product	Work lamp

Accessories

BATTERY SUNMATCH 2/3	03.5375
----------------------	---------