

**HEDI****All-plastic cable drum for F, B, PL and CZ, Type: 40B**

## Order data

Order number	081109 40B
GTIN	4003644007950
Item class	08B

## Description

### Version:

HEDI® cable drums stand for "Made in Germany" quality and a long service life. The drum body is specially designed to optimally guide the cable. The integrated rotation stop switch prevents accidental rotation of the drum. All cable drums are equipped with thermal cut-out switches.

Large, high-quality HEDI® all-plastic cable reel with a reel diameter of 290 mm and numerous ergonomic and safety features.

- **Inclined 7 degrees for greater ground clearance and to make it comfortable to carry.**
- **Removable cable holder and guide for optimum cable control.**
- **Water drainage grooves.**
- **Twist grip for individual right-hand and left-hand operation when winding or unwinding the cable.**
- **Easy to mount on a wall.**
- **Certified for continuous exterior use and for use in humid environments.**

With sockets for **France, Belgium, Poland and the Czech Republic.**

### Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

## Technical description

impact-resistant and splash-proof	Category 2 (K2) to BGI
Cable length	40 m
Material cable	Armoured cable
Cable structure	3G1.5
IP Index of Protection	IP 54
Rated power unrolled	3500 (16 A) W
Cable class	H07BQ-F
Number of sockets	4
Material of body	All-plastic
Nominal voltage	250 V
Power supply	Mains operated
Diagnostic system present	yes
Type of product	Cable drum