



## Pneumatic impact wrench, Type: W2412



### Order data

Order number	079171 W2412
GTIN	7322590052553
Item class	03R

### Description

#### Version:

All technical data relate to a dynamic pressure of **6.3 bar** and the specified hose internal Ø.  
Powerful impact wrench.

Exhaust air passes through the handle, **reversible**.

· **Well balanced and ergonomic.**

#### Application:

Suitable for places where access is difficult and places where space is restricted.

#### Spare part:

**Selected service kits:** Sets of replacement parts for most Atlas Copco pneumatic tools can be supplied on request for preventive maintenance and servicing.

### Technical description

Height	178 mm
Tool arbor drive profile	□
Torque range	100 - 300 Nm
Tool arbor size	1/2 in

Weight	1.4 kg
Length	113 mm
maximum air consumption	780 l/min
Operating noise	88 dB(A)
Maximum screw Ø (8.8 - 12.9)	M16
recommended hose size (internal Ø)	10 mm
maximum speed	7400 min <sup>-1</sup>
maximum vibration to EN	5.6 m/s <sup>2</sup>
Manufacturer's designation	W2412
Format	Pistol
Compressed air connection	1/4 in
Connection thread	BSP
Type of product	Screwdriver