



Safety hose reel, plastic casing Compressed air, Ø 8 × 12 mm, usable hose length: 10Sm



Order data

Order number	080071 10S
GTIN	7391390404046
Item class	08A

Description

Version:

Safety hose reel with **hose guide** and powerful controlled retraction.

Impact resistant enclosed **plastic casing** for use in dirty and dusty environments. Compact design, easy to mount on the wall or ceiling, with **180° swivel angle**. **PU hose** suitable for high throughputs, with high abrasion resistance and steel compressed air connection fittings.

Hose reel with PU hose in **neon green** signal colour.

Note:

For coupling, see No. 080286.

Technical description

usable hose length	10 m
Colour of housing	blue
Colour of hose	neon green
Material of hose	Polyurethane
Connection outlet	1/4 in
maximum operating pressure	16 bar
Material of the housing	Plastic

SCS automatic roll-up drum	yes
Connection inlet	1/4 in
Hose internal Ø	8 mm
Hose external Ø	12 mm
Body width	406 mm
Body depth	190 mm
Body height	313 mm
suitable for	Compressed air
Product name attribute	Ø 8 × 12 mm
Type of product	Hose reel

Accessories

Safety shut-offInternal thread Connection internal thread 1/4 in	080286 1/4
Safety shut-offInternal thread Connection internal thread 1/2 in	080286 1/2
Safety shut-offInternal thread Connection internal thread 3/8 in	080286 3/8