



Sabre saw, Type: SSPE1500X



Order data

Order number	078224 SSPE1500X
GTIN	4002395241699
Item class	03M

Description

Version:

Powerful and robust 1500 W **Milwaukee universal sabre saw** with metal gearbox casing.

- **FIXTEC quick-release saw blade clamping system, no tools required.**
- **Electronic control of rate of strokes, orbital stroke can be switched off.**
- **AVS anti-vibration system and patented eccentric gearbox for very smooth running.**
- **Kick-back protection system to protect the gearbox against kick-backs from the workpiece..**

Function:

IP20: No protection against penetration by foreign bodies with $\varnothing < 12$ mm, however touching should be avoided, and no protection against water.

Supplied with:

Transport case, saw blade.

Note:

Sabre saw blades can be found from No. 588600.

Packaging: Carrying case

Manufacturer's designation: SSPE1500X

Power consumption: 1500 W

Stroke length: 32 mm

Rate of strokes: 0 - 2800 min⁻¹

Weight: 4 kg

maximum vibration to EN: 15.2 m/s²

Technical description

Stroke length	32 mm
---------------	-------

Power consumption	1500 W
Weight	4 kg
Rate of strokes	0 - 2800 min ⁻¹
Manufacturer's designation	SSPE1500X
Special features	FIXTEC / AVS
maximum vibration to EN	15.2 m/s ²
Packaging	Carrying case
Power supply	Mains operated
Type of product	Saw

Accessories

Sabre saw blades set Designation 922EHM	588600 922EHM
Sabre saw blades set Designation 922BF	588600 922BF
Sabre saw blades set Designation 1122BF	588600 1122BF
Sabre saw blades set Designation 922EF	588600 922EF
Sabre saw blades set Designation 1122EF	588600 1122EF
Sabre saw blades set Designation 1155CHM	588600 1155CHM